





PRODUCT NUMBER	PITCH
VYxx01xC00J0G	5.00 mm



RECOMMENDED P.C.B LAYOUT
TOP VIEW

Material:

- Item ① Terminal body(metal housing): Brass, Tin plated
- Item ② Terminal screw: Steel Zinc plating "-" slot type
- Item ③ Wire guard: Stainless steel
- Item ④ Insulator (housing): High temp. polyamide (UL94V-0)

Electrical cULus

- Voltage rating: 300VAC
- Current rating: 15A
- Wire range:
 - Solid wire(AWG): 14-22
 - Stranded wire(AWG): 14-22
- Torque(Lb-In): 3.5
- Screw: M2.6
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Reflow Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C/10Sec max

N=Number of poles
Dim L=Nx5.0
Dim P=(N-1)x5.0

Poles	Dim L	Dim P
2-6p	±0.15	±0.10
7-12p	±0.20	±0.20
13-18p	±0.30	±0.25
19-24p	±0.40	±0.30

PART NO.: VY xx 01 x C 00J0 G

End stackable
No. of poles
02 2 poles
03 3 poles
...
24 24 poles

Body Color
0 Black (RAL9005)

RoHS compliant
(lead<4%)
In copper Alloy

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family			
ltr	ecn	no	dr	date	tolerances unless otherwise specified	MM	TERMINAL BLOCK			
					angles		title			
					tolerances		TERMINAL BLOCK			
					X±0.5		WIRE PROTECTOR, 4SD WIRE INLET, THR			
					X.X±0.3		dwg no			
					X*±1°		sheet 1 of 1 size			
					dr		VYxx01xC00J0G			
					enr		A4			
					chr		type			
					appd		CUSTOMER Drawing			
sheet index	revision	A								
	sheet	1								