
N-Channel 250 V (D-S) MOSFET

PowerPAK® SO-8 Single



Top View Bottom View


FEATURES

- TrenchFET® power MOSFET
- Low thermal resistance PowerPAK® package
- 100 % R_g and UIS tested
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

RoHS COMPLIANT
HALOGEN FREE

APPLICATIONS

- Primary side switch
- Synchronous rectification
- DC/DC converter
- Lighting
- Industrial



N-Channel MOSFET

PRODUCT SUMMARY	
V_{DS} (V)	250
$R_{DS(on)}$ max. (Ω) at V_{GS} = 10 V	0.102
$R_{DS(on)}$ max. (Ω) at V_{GS} = 7.5 V	0.110
Q_g typ. (nC)	11.7
I_D (A)	14.4 [f]
Configuration	Single

ORDERING INFORMATION	
Package	PowerPAK SO-8
Lead (Pb)-free and halogen-free	Si7190ADP-T1-RE3

ABSOLUTE MAXIMUM RATINGS (T_A = 25 °C, unless otherwise noted)

PARAMETER		SYMBOL	LIMIT	UNIT
Drain-source voltage		V_{DS}	250	V
Gate-source voltage		V_{GS}	± 20	
Continuous drain current (T_J = 150 °C)	T_C = 25 °C	I_D	14.4	A
	T_C = 70 °C		11.5	
	T_A = 25 °C		4.3 [a, b]	
	T_A = 70 °C		3.4 [a, b]	
Pulsed drain current (t = 100 µs)		I_{DM}	30	
Continuous source-drain diode current	T_C = 25 °C	I_S	47.3	
	T_A = 25 °C		4.2 [a, b]	
Single pulse avalanche current	L = 0.1 mH	I_{AS}	9	
Single pulse avalanche energy		E_{AS}	4.05	mJ
Maximum power dissipation	T_C = 25 °C	P_D	56.8	W
	T_C = 70 °C		36.4	
	T_A = 25 °C		5 [a, b]	
	T_A = 70 °C		3.2 [a, b]	
Operating junction and storage temperature range		T_J, T_{stg}	-55 to +150	°C
Soldering recommendations (peak temperature) [a]			260	

THERMAL RESISTANCE RATINGS

PARAMETER		SYMBOL	TYPICAL	MAXIMUM	UNIT
Maximum junction-to-ambient [a]	t ≤ 10 s	R_{thJA}	20	25	°C/W
Maximum junction-to-case (drain)	Steady state	R_{thJC}	1.7	2.2	

Notes

a. Surface mounted on 1" x 1" FR4 board
b. t = 10 s
c. See solder profile (www.vishay.com/doc?73257). The PowerPAK SO-8 is a leadless package. The end of the lead terminal is exposed copper (not plated) as a result of the singulation process in manufacturing. A solder fillet at the exposed copper tip cannot be guaranteed and is not required to ensure adequate bottom side solder interconnection
d. Rework conditions: manual soldering with a soldering iron is not recommended for leadless components
e. Maximum under steady state conditions is 68 °C/W
f. T_C = 25 °C

For technical questions, contact: pmostechsupport@vishay.com

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

Downloaded from Arrow.com.

SPECIFICATIONS (T_J = 25 °C, unless otherwise noted)						
PARAMETER	**SYMBOL**	**TEST CONDITIONS**	**MIN.**	**TYP.**	**MAX.**	**UNIT**
Static						
Drain-source breakdown voltage	V_{DS}	V_{GS} = 0 V, I_D = 250 µA	250	-	-	V
V_{DS} temperature coefficient	$\Delta V_{DS}/T_J$	I_D = 250 µA	-	262	-	mV/°C
$V_{GS(th)}$ temperature coefficient	$\Delta V_{GS(th)}/T_J$		-	-7	-	
Gate-source threshold voltage	$V_{GS(th)}$	V_{DS} = V_{GS}, I_D = 250 µA	2	-	4	V
Gate-source leakage	I_{GSS}	V_{DS} = 0 V, V_{GS} = ± 20 V	-	-	100	nA
Zero gate voltage drain current	I_{DSS}	V_{DS} = 250 V, V_{GS} = 0 V	-	-	1	µA
		V_{DS} = 250 V, V_{GS} = 0 V, T_J = 70 °C	-	-	10	
On-state drain current [a]	$I_{D(on)}$	$V_{DS} \geq$ 5 V, V_{GS} =10 V	10	-	-	A
Drain-source on-state resistance [a]	$R_{DS(on)}$	V_{GS} =10 V, I_D = 4.3 A	-	0.085	0.102	Ω
		V_{GS} = 7.5 V, I_D = 4.1 A	-	0.088	0.110	
Forward transconductance [a]	g_{fs}	V_{DS} = 15 V, I_D = 4.3 A	-	11	-	S
Dynamic [b]						
Input capacitance	C_{iss}	V_{DS} = 100 V, V_{GS} = 0 V, f = 1 MHz	-	860	-	pF
Output capacitance	C_{oss}		-	85	-	
Reverse transfer capacitance	C_{rss}		-	7	-	
Total gate charge	Q_g	V_{DS} = 125 V, V_{GS} = 10 V, I_D = 4.3 A	-	14.9	22.4	nC
		V_{DS} = 125 V, V_{GS} = 7.5 V, I_D = 4.3 A	-	11.7	17.6	
Gate-source charge	Q_{gs}		-	3.9	-	
Gate-drain charge	Q_{gd}		-	3.7	-	
Output charge	Q_{oss}	V_{DS} = 125 V, V_{GS} = 0 V	-	24.5	37	Ω
Gate resistance	R_g	f = 1 MHz	0.48	2.4	4.8	Ω
Turn-on delay time	$t_{d(on)}$	V_{DD} = 125 V, R_L = 36.8 Ω, $I_D \cong$ 3.4 A, V_{GEN} = 10 V, R_g = 1 Ω	-	13	30	ns
Rise time	t_r		-	5	15	
Turn-off delay time	$t_{d(off)}$		-	23	40	
Fall time	t_f		-	10	20	
Turn-on delay time	$t_{d(on)}$	V_{DD} = 125 V, R_L = 36.8 Ω, $I_D \cong$ 3.4 A, V_{GEN} = 7.5 V, R_g = 1 Ω	-	15	30	
Rise time	t_r		-	7	15	
Turn-off delay time	$t_{d(off)}$		-	25	40	
Fall time	t_f		-	12	25	
Drain-Source Body Diode Characteristics						
Continuous source-drain diode current	I_S	T_C = 25 °C	-	-	47.3	A
Pulse diode forward current	I_{SM}		-	-	30	
Body diode voltage	V_{SD}	I_S = 3.4 A, V_{GS} = 0 V	-	0.75	1.2	V
Body diode reverse recovery time	t_{rr}	I_F = 3.4 A, di/dt = 100 A/µs, T_J = 25 °C	-	100	150	ns
Body diode reverse recovery charge	Q_{rr}		-	420	630	nC
Reverse recovery fall time	t_a		-	70	-	ns
Reverse recovery rise time	t_b		-	30	-	

Notes

a. Pulse test; pulse width ≤ 300 µs, duty cycle ≤ 2 %


b. Guaranteed by design, not subject to production testing

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.


For technical questions, contact: pmostechsupport@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

Downloaded from Arrow.com.


TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Output Characteristics




Transfer Characteristics




On-Resistance vs. Drain Current and Gate Voltage



Capacitance




Gate Charge




On-Resistance vs. Junction Temperature

For technical questions, contact: pmostechsupport@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000
Downloaded from Arrow.com.


TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Source-Drain Diode Forward Voltage




Threshold Voltage



On-Resistance vs. Gate-to-Source Voltage




Single Pulse Power, Junction-to-Ambient




Safe Operating Area, Junction-to-Ambient

For technical questions, contact: pmostechsupport@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000
Downloaded from Arrow.com.


TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)



Current Derating [a]



Power, Junction-to-Case




Power, Junction-to-Ambient

Note


a. The power dissipation P_D is based on T_J max. = 150 °C, using junction-to-case thermal resistance, and is more useful in settling the upper dissipation limit for cases where additional heatsinking is used. It is used to determine the current rating, when this rating falls below the package limit

For technical questions, contact: pmostechsupport@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000
Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)



Normalized Thermal Transient Impedance, Junction-to-Ambient




Normalized Thermal Transient Impedance, Junction-to-Foot

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package / tape drawings, part marking, and reliability data, see www.vishay.com/ppg?75633.

For technical questions, contact: pmostechsupport@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000
Downloaded from Arrow.com.

PowerPAK® SO-8, (Single/Dual)



Notes


1. Inch will govern.
2. Dimensions exclusive of mold gate burrs.
3. Dimensions exclusive of mold flash and cutting burrs.

DIM.	MILLIMETERS			INCHES		
	MIN.	NOM.	MAX.	MIN.	NOM.	MAX.
A	0.97	1.04	1.12	0.038	0.041	0.044
A1		-	0.05	0	-	0.002
b	0.33	0.41	0.51	0.013	0.016	0.020
c	0.23	0.28	0.33	0.009	0.011	0.013
D	5.05	5.15	5.26	0.199	0.203	0.207
D1	4.80	4.90	5.00	0.189	0.193	0.197
D2	3.56	3.76	3.91	0.140	0.148	0.154
D3	1.32	1.50	1.68	0.052	0.059	0.066
D4	0.57 typ.			0.0225 typ.		
D5	3.98 typ.			0.157 typ.		
E	6.05	6.15	6.25	0.238	0.242	0.246
E1	5.79	5.89	5.99	0.228	0.232	0.236
E2	3.48	3.66	3.84	0.137	0.144	0.151
E3	3.68	3.78	3.91	0.145	0.149	0.154
E4	0.75 typ.			0.030 typ.		
e	1.27 BSC			0.050 BSC		
K	1.27 typ.			0.050 typ.		
K1	0.56	-	-	0.022	-	-
H	0.51	0.61	0.71	0.020	0.024	0.028
L	0.51	0.61	0.71	0.020	0.024	0.028
L1	0.06	0.13	0.20	0.002	0.005	0.008
θ	0°	-	12°	0°	-	12°
W	0.15	0.25	0.36	0.006	0.010	0.014
M	0.125 typ.			0.005 typ.		
ECN: S17-0173-Rev. L, 13-Feb-17 DWG: 5881						

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

Downloaded from Arrow.com.

RECOMMENDED MINIMUM PADS FOR PowerPAK® SO-8 Single



Recommended Minimum Pads
Dimensions in Inches/(mm)

Return to Index

APPLICATION NOTE

Downloaded from Arrow.com.

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, “Vishay”), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

© 2026 VISHAY INTERTECHNOLOGY, INC. ALL RIGHTS RESERVED

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

Downloaded from Arrow.com.