

1436411

https://www.phoenixcontact.com/us/products/1436411

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector front mounting, Universal, 5-position, Pin, straight, M12-Standard, coding: A, on free cable end, Front mounting, M16 x 1.5, Individual wires, cable length: 0.5 m, 0.34 mm^2 , TPE litz wire, potted

Your advantages

- · Preassembled with litz wires for immediate use
- · Customer-specific assemblies and litz wire lengths available
- · Standard pin assignments and codings for signal transmission with a uniform design-in design

Commercial data

Item number	1436411
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB24
Product key	ABQCMB
Catalog page	Page 241 (C-2-2013)
GTIN	4046356438360
Weight per piece (including packing)	26.4 g
Weight per piece (excluding packing)	16.2 g
Customs tariff number	85444290
Country of origin	DE



1436411

https://www.phoenixcontact.com/us/products/1436411

Technical data

Notes

nes	
Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
General	Contact connection method: Crimp connection
Safety note	
Safety note	WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.
	 WARNING: Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible.
	 WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.
	 The products are suitable for applications in plant, controller, and electrical device engineering.
	 When operating the connectors in outdoor applications, they must be separately protected against environmental influences.
	 Assembled products may not be manipulated or improperly opened.
	 Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at phoenixcontact.com/products).
	 When using the product in direct connection with third-party manufacturers, the user is responsible.
	 For operating voltages > 50 V AC, conductive connector housings must be grounded
	 Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards.
	Observe the corresponding technical data. You will find information: o On the product o On the packing label o In the supplied documentation o Online at phoenixcontact.com/products under the product
	Only use tools recommended by Phoenix Contact

• Use a protective cap to protect connectors that are not in use. The suitable accessories are available online in the accessory



1436411

https://www.phoenixcontact.com/us/products/1436411

	section of the product at phoenixcontact.com/products
	 Ensure that the protective or functional ground has been properly connected.
	 VDE 0100/1.97 § 411.1.3.2 and DIN EN 60 204/11.98 § 14.1.3 are applicable when combining several circuits in a cable and/or connector
	 The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting warnings (e.g. DIN EN ISO 13732-1:2008-12).
unting	
Mounting type	Front mounting M16 x 1.5
oduct properties	
Product type	Circular connectors (device side)
Application	Signal
Sensor type	Universal
Number of positions	5
No. of cable outlets	1
Shielded	no
Coding	A
Thread type	M12
	····2
nsulation characteristics	II
Overvoltage category Degree of pollution	3
terial specifications Color	black
Material Molding compound	PUR (potted)
Flammability rating according to UL 94	HB
Seal material	Viton
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA 6.6
Material for screw connection	PA 6.6
Conductor material	Tin-plated Cu litz wires
atrical proportion	
ctrical properties	4.5.17
Rated surge voltage	1.5 kV
Rated surge voltage Contact resistance	≤ 3 mΩ
Rated surge voltage	



1436411

https://www.phoenixcontact.com/us/products/1436411

Nominal current I _N	4 A
Max. conductor resistance	80 Ω/km

Connection data

Conductor connection

Connection method	Individual wires
Contact connection type	Pin
Conductor cross section	0.34 mm²
Tightening torque	1.25 Nm 1.5 Nm (Installation-side)

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Connector

Connection 1

Head design	Pin
Head cable outlet	straight
Head thread type	M12
Head locking type	Standard
Coding	A

Connection 2

Head design	free cable end
-------------	----------------

Cable/line

Cable length	0.5 m
Cable type	TPE litz wire
Signal type/category	Universal
Wire diameter incl. insulation	1.2 mm ±0.07 mm
Single wire, color	black, brown,blue, white, gray
Cable cross section	0.34 mm²
Conductor material	Tin-plated Cu litz wires
Conductor structure signal line	7x 0.25 mm
AWG signal line	24
Material wire insulation	TPE
Thickness, insulation	0.21 mm
Nominal voltage, cable	300 V
Test voltage, cable	2000 V AC
Cable resistance	≤ 80 Ω/km
Cable insulation resistance	≥ 20 MΩ*km
Ambient temperature (operation)	-40 °C 85 °C (cable, fixed installation)



1436411

https://www.phoenixcontact.com/us/products/1436411

Standards/specifications

	-25 °C 85 °C (Cable, flexible installation)			
Environmental and real-life conditions				
Ambient conditions				
Degree of protection	IP67			
	IP67			
Ambient temperature (operation)	-25 °C 85 °C (Plug / socket)			
	-40 °C 85 °C (without mechanical actuation)			
	-25 °C 85 °C (Cable, flexible installation)			
	-40 °C 85 °C (cable, fixed installation)			
UL Type Rating	Type 4 (indoor use only)			
Standards and regulations				
Standard designation	M12 circular connector			


according to IEC 61076-2-101




1436411

https://www.phoenixcontact.com/us/products/1436411

Drawings



Pin assignment M12 male connector, 5-pos., A-coded, male side



I = current strength, T = ambient temperature



1436411

https://www.phoenixcontact.com/us/products/1436411

Circuit diagram



Contact assignment of the M12 plug



1436411

https://www.phoenixcontact.com/us/products/1436411

Classifications

UNSPSC 21.0

_	\sim		0	0
F	C	ı A	เร	. ``

	ECLASS-13.0	27440103		
ETIM				
	ETIM 9.0	EC003570		
UNSPSC				

39121400



1436411

https://www.phoenixcontact.com/us/products/1436411

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	89fbf4ff-aefd-4225-aac6-cd3ce1b35893

Phoenix Contact 2025 @ - all rights reserved https://www.phoenixcontact.com

Phoenix Contact USA 586 Fulling Mill Road Middletown, PA 17057, United States (+717) 944-1300 info@phoenixcon.com