

# WSGPA01

# 10 W, 5 GHz, GaN on SiC General Purpose Power Amplifier

## **Description**

The WSGPA01 is a GaN on SiC Discrete General Purpose Amplifier (GPA) designed for applications up to 5 GHz. The device operates from supply voltages up to 50 V and can achieve a P<sub>3dB</sub> of 10 W. It is housed in a 3 mm X 4 mm DFN package. While it is designed for communications infrastructure applications with crest factor reduced and digitally pre-distorted LTE or 5G NR signals, it may be suitable for other applications at frequencies up to 5 GHz, restricted only by its maximum operating conditions.

#### **Features**

GaN on SiC HEMT technology

Operating frequency: up to 5 GHz

P<sub>3dB</sub>: up to 10 W

Supply voltage: up to 50 V

Maximum junction temperature: 225 °C

• Pb-free and RoHS compliant



WSGPA01 Package PG-DFN-3x4-1

#### **RF Performance**

Typical Single-carrier WCDMA Performance (tested in the test fixture)

 $V_{DD}$  = 48 V,  $I_{DO}$  = 25 mA,  $P_{OUT}$  = 26.5 dBm, channel bandwidth = 3.84 MHz, input PAR = 10 dB @ 0.01% CCDF

Frequency	P <sub>OUT</sub> (dBM)	Gain (dB)	Efficiency (%)	ACPR – (dBc)	ACPR + (dBc)	PAR (dB)
3400 MHz	26.5	16.1	16.9	-47.8	-48.6	9.3
3600 MHz	26.5	16.0	15.7	-49.1	-49.9	9.4
3800 MHz	26.5	15.7	16.5	-46.9	-47.2	9.3



All published data at T<sub>AMBIENT</sub> = 25°C unless otherwise indicated



# Absolute Maximum Ratings (Case Temperature T<sub>CASE</sub> = 25 °C)

Parameter	Symbol	Value	Unit
Drain-source Voltage	$V_{DSS}$	125	V
Gate-source Voltage	$V_{GS}$	-10 to +2	V
Gate Current	I <sub>G</sub>	1.2	mA
Drain Current	I <sub>D</sub>	400	mA
Operating Voltage	$V_{DD}$	55	V
Junction Temperature	TJ	225	°C
Storage Temperature Range	T <sub>STG</sub>	-65 to +150	°C

Operation above the maximum values listed here may cause permanent damage. Maximum ratings are absolute ratings; exceeding only one of these values may cause irreversible damage to the component. Exposure to absolute maximum rating conditions for extended periods may affect device reliability. For reliable continuous operation, the device should be operated within the operating voltage range  $(V_{DD})$  specified above.

#### **DC Characteristics**

Characteristics	Conditions	Symbol	Min	Тур	Max	Unit
Drain-Source Breakdown Voltage	$V_{GS} = -8 \text{ V}, I_D = 10 \text{ mA}$	V <sub>(BR)DSS</sub>	150	_	_	V
Drain-Source Leakage Current	$V_{GS} = -8 \text{ V}, V_{DS} = 50 \text{ V}$	I <sub>GSS</sub>	_	_	-0.5	mA
Gate Threshold Voltage	V <sub>DS</sub> = 10 V, I <sub>D</sub> = 1.2 mA	V <sub>GS(th)</sub>	-3.8	-3.1	-2.3	V

# **Recommended Operating Conditions**

Parameter	Conditions	Symbol	Min	Тур	Max	Unit
Drain Operating Voltage		$V_{DD}$	0	_	50	V
Gate Quiescent Voltage	$V_{DS} = 48 \text{ V}, I_D = 25 \text{ mA}$	$V_{GS(Q)}$	-3.45	-2.9	-2.45	V

#### **Thermal Characteristics**

Characteristics	Symbol	Value	Unit
Thermal Resistance (T <sub>CASE</sub> = 105°C, P <sub>OUT</sub> = 26.5 dBM CW)	$R_{ hetaJC}$	10.1	°C/W

## **Moisture Sensitivity Level**

Level	Test Standard	Package Temperature	Unit
3	IPC/JEDEC J-STD-020	260	°C

### **ESD Characteristics**

Parameter	Class	Standard
Human Body Model (HBM)	Class 1A	ANSI/ESDA/JEDEC JS-001
Charge Device Model (CDM)	Class C2b	ANSI/ESDA/JEDEC JS-002



#### **RF Characteristics**

Single-carrier WCDMA Performance (tested in the production test fixture)

 $V_{DD} = 48 \text{ V}, I_{DQ(MAIN)} = 25 \text{ mA}, P_{OUT} = 26.5 \text{ dBm}, f = 3600 \text{ MHz}, channel bandwidth} = 3.84 \text{ MHz}, input PAR = 10 \text{ dB} @ 0.01\% \text{ CCDF}$ 

Characteristics	Symbol	Min	Тур	Max	Unit
Gain	G <sub>ps</sub>	14.8	16.3	_	dB
Drain Efficiency	$\eta_{\text{D}}$	14	18.2	_	%
Adjacent Channel Power Ratio	ACPR	_	-45.4	-41	dBc
Output PAR @ 0.01% CCDF	OPAR	8	9.1	_	dB

# **Ordering Information**

Order Code	Description
WSGPA01-V1-R1	330 mm (13") Reel 100 pcs
WSGPA01-V1-R7	330 mm (13") Reel 750 pcs
WSGPA01-V1-R3K	330 mm (13") Reel 3,000 pcs
FXA/WSGPA01V1-19	2.496–2.690 GHz Evaluation Board
FXA/WSGPA01V1-14	3.3-3.7 GHz Evaluation Board
FXA/WSGPA01V1-15	3.4-3.8 GHz Evaluation Board
FXA/WSGPA01V1-18	3.7-3.98 GHz Evaluation Board

#### **Evaluation Boards**


**Single-carrier WCDMA Performance** (tested in the test fixture)

 $V_{DD}$  = 48 V,  $I_{DQ}$  = 25 mA, channel bandwidth = 3.84 MHz, input PAR = 10 dB @ 0.01% CCDF

		Typical RF Performance						
Part Number	Frequency	P <sub>OUT</sub> (dBm)	Eff (%)	Gain (dB)	PAR (dB)	ACPR- (dBc)	ACPR+ (dBc)	
FXA/WSGPA01V1-19	2.496-2.690 GHz	25	17.1	19.4	8.5	-36.7	-36.9	
FXA/WSGPA01V1-14	3.3-3.7 GHz	26.5	18	16	8.9	-45.1	-45.8	
FXA/WSGPA01V1-15	3.4-3.8 GHz	26.5	15.7	16	9.4	-49.9	-49.1	
FXA/WSGPA01P3-18	3.7-3.98 GHz	26.5	17.5	16.8	9.1	-46.3	-45.2	



## Pinout Diagram (top view)



## **Bias Sequencing**

#### **Bias ON**


- 1. Ensure RF is turned off
- 2. Apply pinch-off voltage of –5 V to the gate
- 3. Apply nominal drain voltage
- 4. Bias gate to desired quiescent drain current
- 5. Apply RF

#### **Bias OFF**

- 1. Turn RF off
- 2. Apply pinch-off voltage to the gate
- 3. Turn-off drain voltage
- 4. Turn-off gate voltage




## **Tape and Reel Information**





# **Package Outline Specifications**





#### Notes & Disclaimer

MACOM Technology Solutions Inc. ("MACOM"). All rights reserved.

These materials are provided in connection with MACOM's products as a service to its customers and may be used for informational purposes only. Except as provided in its Terms and Conditions of Sale or any separate agreement, MACOM assumes no liability or responsibility whatsoever, including for (i) errors or omissions in these materials; (ii) failure to update these materials; or (iii) conflicts or incompatibilities arising from future changes to specifications and product descriptions, which MACOM may make at any time, without notice. These materials grant no license, express or implied, to any intellectual property rights.

THESE MATERIALS ARE PROVIDED "AS IS" WITH NO WARRANTY OR LIABILITY. EXPRESS OR IMPLIED. RELATING TO SALE AND/OR USE OF MACOM PRODUCTS INCLUDING FITNESS FOR A PARTICULAR PURPOSE, MERCHANTABILITY, INFRINGEMENT OF INTELLECTUAL PROPERTY RIGHT, ACCURACY OR COMPLETENESS, OR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES WHICH MAY RESULT FROM USE OF THESE MATERIALS.

MACOM products are not intended for use in medical, lifesaving or life sustaining applications. MACOM customers using or selling MACOM products for use in such applications do so at their own risk and agree to fully indemnify MACOM for any damages resulting from such improper use or sale.

Downloaded from Arrow.com.