

FL SWITCH 4004T-8POE-4SFP - Industrial Ethernet Switch



1026922

<https://www.phoenixcontact.com/us/products/1026922>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Managed PoE Switches 4000, 4 RJ45 ports 10/100/1000 Mbps, 4 SFP ports 1000 Mbps, 8 RJ45 ports 10/100/1000 Mbps

Product description

FL SWITCH 4000 managed industrial PoE Ethernet switches combine Gigabit interfaces with extensive network performance for the most demanding applications. Security features with complete IEEE redundancy (STP/RSTP/MST) and 15 ms recovery time extended ring redundancy optimize network uptime. Unique web customization provides a simplified user interface for today's applications and scalable functionality for future needs. A comprehensive mix of 10/100/1000 Mbps RJ45, PoE functionality and Gigabit fiber optic connections combine performance with installed cost savings.

Your advantages

- -40 °C to 75 °C ambient temperature
- Twelve 10/100/1000 Mbps RJ45 ports for device connections and four SFP-based fiber optic LC interfaces for network trunk lines.
- Redundant power supply
- Wide -40° ... +75°C temperature range
- VLANs
- DHCP client
- MSTP
- RSTP
- Web-based management, SNMP
- Secure web-based and SNMP-based management
- Extensive web diagnostics with configurable LED and remote alarm contacts
- Unique cleanup function hides unused configuration pages, reducing complexity, maintenance and startup times

Commercial data

Item number	1026922
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN17
Product key	DNN125
Catalog page	Page 319 (C-6-2019)
GTIN	4055626519548
Weight per piece (including packing)	1,757 g
Weight per piece (excluding packing)	1,398 g
Customs tariff number	85176200

FL SWITCH 4004T-8POE-4SFP - Industrial Ethernet Switch



1026922
<https://www.phoenixcontact.com/us/products/1026922>

Country of origin	TW
-------------------	----

FL SWITCH 4004T-8POE-4SFP - Industrial Ethernet Switch



1026922

<https://www.phoenixcontact.com/us/products/1026922>

Technical data

Dimensions

Width	68 mm
Height	170 mm
Depth	152 mm

Notes

Notes on operation	Designed to function with all 48 V DC QUINT and TRIO power supplies.
Notes on operation	Mode A or Mode B PoE

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Material specifications

Housing material	Aluminum
------------------	----------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

Interfaces

Ethernet (RJ45)

Connection method	RJ45
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100/1000 Mbps
Transmission physics	Ethernet in RJ45 twisted pair
Transmission length	100 m (per segment)
Signal LEDs	Data receive, link status
No. of channels	4 (RJ45 ports)

Ethernet (SFP)

Connection method	SFP
Transmission speed	1000 Mbps (full duplex)
Transmission physics	Depending on the SFP module
Transmission length	up to 80 km (Depending on the fiber/SFP module used)
Signal LEDs	Data receive, link status
No. of channels	4 (SFP ports)

Ethernet (PoE)

Connection method	RJ45
Note on the connection method	Auto negotiation and autocrossing

FL SWITCH 4004T-8POE-4SFP - Industrial Ethernet Switch



1026922

<https://www.phoenixcontact.com/us/products/1026922>

Transmission speed	10/100/1000 Mbps
Transmission physics	Ethernet in RJ45 twisted pair
Transmission length	100 m
No. of channels	8 (RJ45 ports)

Product properties

Product type	Switch
Product family	Managed PoE Switches 4000
Type	Block design
MTTF	14.8 Years (MIL-HDBK-217F standard, temperature 25°C, operating cycle 100%)

Data management status

Article revision	03
------------------	----

Switch functions

Diagnostic functions	RMON History
	LLDP (Link Layer Discovery Protocol)
	SNMP-Traps
	N:1-Portmirroring
Basic functions	Store and forward switch, Multicast control, IGMP snooping, trunking, Port and Tagging VLANs, Port and IEEE 802.1x security, SNMP V3 and Https security, SNTP, web customization, user access control to functions, Modbus/TCP, PoE according to IEEE 802.3at/af.
Filter functions	Quality of Service (8 and 64 priority classes)
	Port prioritization
	VLAN (up to 64 VLANs)
	IGMP Snooping (256 groups)
	IGMP Query
IP parameterization	DHCP client
	BootP
MAC address table	16k
Management	Web-based management (HTTP/HTTPS)
	SNMPv1/v2/v3
Redundancy	RSTP (Rapid Spanning Tree Protocol)
	MSTP (Multiple Spanning Tree Protocol)
Status and diagnostic indicators	LEDs: U _{S1} , U _{S2} (redundant voltage supply), Alarm (alarm contact), Link/Activity and PoE per Ethernet port
Additional functions	Transmission of MMS and GOOSE (IEC 61850-8-1)
Time synchronization	SNTP (Simple Network Time Protocol)

Security functions

Basic functions	Store and forward switch, Multicast control, IGMP snooping, trunking, Port and Tagging VLANs, Port and IEEE 802.1x security, SNMP V3 and Https security, SNTP, web customization, user access control to functions, Modbus/TCP, PoE according to IEEE 802.3at/af.
-----------------	---

FL SWITCH 4004T-8POE-4SFP - Industrial Ethernet Switch



1026922

<https://www.phoenixcontact.com/us/products/1026922>

Electrical properties

Local diagnostics	US1, US2 Supply voltage Green LED
	LNK/ACT Link status/data transmission Green LED
	PoE PoE detection Orange LED
	Alarm Power failure at US1 or US2/Link failure
Maximum power dissipation for nominal condition	260 W (at 55V DC)
Transmission medium	Copper
	FO

Supply

Supply voltage (DC)	55 V DC (redundant)
Supply voltage range	52 V DC ... 57 V DC (> 52 V DC for PoE+ or 60 W output recommended)
Inrush current	42 A (52 V DC for 3140 µs)
Residual ripple	3.6 V _{PP} (within the permitted voltage range)
Max. current consumption	4.8 A (Maximum, nominal load)
Typical current consumption	301 mA (U _S = 55 V DC)

Connection data

Connection technology

Connection name	Power supply
pluggable	yes

Power supply

Connection method	Screw connection
Conductor cross section, rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross section, flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross section AWG	24 ... 12
Stripping length	7 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP30
Ambient temperature (operation)	-40 °C ... 75 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	2000 m (above sea level)
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Air pressure (operation)	57 kPa ... 108 kPa (up to 4850 m above mean sea level)
Air pressure (storage/transport)	57 kPa ... 108 kPa (up to 4850 m above mean sea level)

Approvals

Conformity/Approvals

1026922
<https://www.phoenixcontact.com/us/products/1026922>

Conformance	CE-compliant
-------------	--------------

EMC data

Conformance with EMC directives	IEC 61000-6-2 IEC 61000-4-2 (ESD) Criterion B
	IEC 61000-4-3 (immunity to radiated interference) Criterion A
	IEC 61000-4-4 (burst) Criterion A
	IEC 61000-4-5 (surge) Criterion B
	IEC 61000-4-6 (immunity to conducted interference) Criterion A
	IEC 61000-4-8 (immunity to magnetic fields) Criterion A
	EN 55022 (emitted interference) Criterion A
Noise immunity	EN 61000-6-2:2005
Electromagnetic compatibility	Conformance with EMC Directive 2004/108/EC
Noise emission	EN 61000-6-4

System properties

Functionality	
Basic functions	Store and forward switch, Multicast control, IGMP snooping, trunking, Port and Tagging VLANs, Port and IEEE 802.1x security, SNMP V3 and Https security, SNTP, web customization, user access control to functions, Modbus/TCP, PoE according to IEEE 802.3at/af.

Signaling

Status display	LEDs: U _{S1} , U _{S2} (redundant voltage supply), Alarm (alarm contact), Link/Activity and PoE per Ethernet port
----------------	--

FL SWITCH 4004T-8POE-4SFP - Industrial Ethernet Switch



1026922

<https://www.phoenixcontact.com/us/products/1026922>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1026922>



EAC

Approval ID: RU*-DE.*.B.00741/19



UL Listed

Approval ID: E238705



cUL Listed

Approval ID: E238705

UAE-RoHS

Approval ID: 23-09-84494

cULus Listed

1026922
<https://www.phoenixcontact.com/us/products/1026922>

Classifications

ECLASS

ECLASS-11.0	19170401
ECLASS-12.0	19170401
ECLASS-13.0	19170401

ETIM

ETIM 9.0	EC000734
----------	----------

UNSPSC

UNSPSC 21.0	43222600
-------------	----------

1026922
<https://www.phoenixcontact.com/us/products/1026922>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	15(a), 6(c), 7(a), 7(c)-I
China RoHS	
Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	6e5bc006-0d72-4ef1-9cab-4198c4460f35

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com