

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2005

© COPYRIGHT 2005

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN


APVD

ERGOCRIMP DIE SET FOR MCON 2.8LL TERMINALS - 1,5 - 2,5 mm²

Ersatzmatrize fuer Ergocrimp Handzange PN 9-1579004-8
Spare die set for Ergocrimp hand tool PN 9-1579004-8

Matrize in Kombination mit Ergocrimp Basishandzange PN 539635-1 verwendbar
Spare die set usable in combination with Ergocrimp basis hand tool PN 539635-1

Matrize im Karton mit Bedienungsanleitung 411-18416 verpackt
Die set packed in a cardboard with instruction sheet 411-18416




9-1579021-2	1	0-0744012-7	Instruction Sheet	Bedienungsanleitung	6
	1	0-0519024-2	Nut M4 DIN 985	Mutter M4 DIN 985	5
	1	1-0519151-3	Screw M4x25	Schraube M4x25	4
	1	1-0519151-1	Screw M4x16	Schraube M4x16	3
	1	4-1579003-6	Locator Assembly	Drahtanschlag	2
	1	4-1579003-5	Contact Locator	Kontaktpositionierer	1
	QTY Stck	PN	Description	Benennung	Pos.

Kontakt	DGB (mm ²)	Drahtcrimp / Wire Crimp		Isolationscrimp/Insulationcrimp		Isol.Ø	Betriebsanl.
Contact	Wire Range	Hoehe/Height mm	Breite/Width mm	Hoehe/Height mm	Breite/Width mm	Ins.Range	Instr.Sheet
1719841	1.50	1.48 ±0.05	2,79 F	3.20	3.94 0V	2.2-2.4	411-18416
	2.50	1.77 ±0.05		3.30		2.7-3.0	

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:

mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES	±1°

MATERIAL

FINISH

DWN 02MAY2007

Ch.Witt

CHK

-

APVD

-

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

200 g

tyco
Electronics

tyco Electronics AMP GmbH

D - 64625 Bensheim

NAME

ERGOCRIMP DIE SET FOR
MCON 2.8LL 1,5-2,5 mm²

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-9-1579021-2

-

CUSTOMER DRAWING

SCALE 2:1

SHEET 1 OF 1

REV A