


UMKS- C64F-VS - Interface module



2970578

<https://www.phoenixcontact.com/us/products/2970578>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, for IEC 603/DIN 41612 connector, type C, 64-pos., a, c components mounted, with socket strip, cable housing with screw interlock

Commercial data

Item number	2970578
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C422
Product key	CK2187
Catalog page	Page 290 (IF-2009)
GTIN	4017918087760
Weight per piece (including packing)	335.7 g
Weight per piece (excluding packing)	3.33 g
Customs tariff number	85369010
Country of origin	DE

UMKS- C64F-VS - Interface module



2970578

<https://www.phoenixcontact.com/us/products/2970578>

Technical data

Product properties

Product type	Interface module
Product family	VARIOFACE
Number of positions	64

Insulation characteristics

Insulation	Basic insulation
------------	------------------

Insulation characteristics

Insulation	Basic insulation
Overvoltage category	III
Pollution degree	2

Electrical properties

Nominal voltage U_N	125 V AC/DC
Max. current carrying capacity per branch	1 A
Rated surge voltage	4 kV

Connection data

Field level

Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross section rigid	0.2 mm ² ... 4 mm ²
Conductor cross section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross section AWG	24 ... 12

Controller level

Connection method	IEC 603/DIN 41612 connection
Number of connections	1
Number of positions	64

Signaling

Status display present	No
------------------------	----

Dimensions

Item dimensions

Width	134.8 mm
Height	77 mm
Depth	70.87 mm

UMKS- C64F-VS - Interface module



2970578

<https://www.phoenixcontact.com/us/products/2970578>

Material specifications

Color	green (RAL 6021)
Housing insulation material	Polyamide PA non-reinforced

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Standards and regulations

Standards/regulations	IEC 60664
	DIN EN 50178

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

UMKS- C64F-VS - Interface module



2970578

<https://www.phoenixcontact.com/us/products/2970578>

Classifications

ECLASS

ECLASS-11.0	27141152
-------------	----------

UNSPSC

UNSPSC 21.0	39121432
-------------	----------

UMKS- C64F-VS - Interface module



2970578

<https://www.phoenixcontact.com/us/products/2970578>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com