

Military/Aerospace High Performance Relays

Product Highlights:

- [View all Features](#) | [Find Similar Products](#)

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)
[Request Samples](#)



TE Internal Number: 6 -
1617090 - 0

 Active

 [Add to Part List](#)

Product Drawings:

- ## Catalog Pages/Data Sheets:

- ? [RELAY](#) (PDF, English)

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

List all Documents

Additional Information:

- ## ? Product Line Information

Related Products:

- ## ? Tooling

Product Type Features:

- ? Termination Type = Solder Hook Terminals

Electrical Characteristics:

- ? Input Voltage (VDC) = 26.5
- ? Contact Current Rating (Amps.) = 2
- ? Coil Polarity Protection Diode = Without
- ? Transistor Driver = Without
- ? Coil Resistance (?) = 1000
- ? MOSFET Driver = Without
- ? Coil Power Measurement = Milliwatts
- ? Coil Power, Nominal (mW) = 702
- ? Actuating System = DC
- ? Shock = 100G's, 6ms
- ? Vibration = 30G's, 10 to 2500Hz

Body Related Features:

- ? Series = LS Half -size Relay

Contact Related Features:

- ? Mounting Options = Panel Mount
- ? Enclosure = Hermetically Sealed

Configuration Related Features:

- ? Contact Arrangement = 2 Form C, DPDT, 2 C/O
- ? Coil Magnetic System = Polarized, Bistable
- ? Coil Suppression Diode = Without
- ? Coil Latching = Double

Industry Standards:

- ? Government/Industry Qualification = No
- ? RoHS/ELV Compliance = Not ELV/RoHS compliant
- ? Lead Free Solder Processes = Not suitable for lead free processing

Conditions for Usage:

- ? Temperature Range (°C) = -65 – +125

Other:

- ? Brand = CII