

COAXIAL CONNECTOR, PC 2.4, 50 Ohm, Straight PCB jack (female)

82_PC24-S50-0-201/199_N

Properties

- For stripline configurations
- Fast and easy installation
- Precision testing up to 50 GHz
- Reusable design
- Mechanical intermateable with PC 1.85 (1.85 mm standard)



Product configuration		
Interface type	Gender	Standard
PC 2.4	jack	MIL-STD-348B
Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Stainless steel	Passivated (Plating)
Insulator	PEI (Polyether-imide)	
Electrical data		
Impedance	50 Ω	
Interface frequency	50 GHz	
Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
0 GHz ... 50 GHz	20 dB	1.22
Mechanical data		
Weight	0.0024 kg	
Mating cycles	500	
Environmental data		
Operation temperature	-40 °C ... 165 °C	

COAXIAL CONNECTOR, PC 2.4, 50 Ohm, Straight PCB jack (female)

82_PC24-S50-0-201/199_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
85221624	RoHS 2011/65/EU and (EU) 2015/863	Compliant without exemption	
	REACH 1907/2006 Article 33 SVHC	Free of SVHC >0,1%	

Ordering Information Table	
Item number	Item description
85221624	82_PC24-S50-0-201/199_NE

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P41022 / Date of publication: 12.07.2025 / uncontrolled copy