






PRODUCT NUMBER

PITCH

0Qxx75x100J0G

5.00 mm

RECOMMENDED P.C.B LAYOUT
TOP VIEW

DIMENSION

Dim A	(N+2)×5.0
Dim B&C	(N-1)×5.0
Dim D	(N+1)×5.0

N= NUMBER OF POLES

Poles	Tolerance
2P-6P	±0.15
7P-12P	±0.20
13P-18P	±0.25
19P-24P	±0.30

PART NO.: 0Q xx 75 x 1 00J0 G

No. of poles	Body Color	RoHS compliant (lead<4%)
02 2 poles	0 Black (RAL9005)	In copper Alloy
03 3 poles	2 Red (RAL3001/D)	
...	3 Orange(RAL2011/P)	
24 24 poles	4 Yellow(RAL1018/A)	
	5 Green(RAL6018/T)	
	6 Blue (RAL5015/A)	
	8 Grey(RAL7035/D)	
	9 White(RAL1102)	
	C Green(RAL6018/U)	

mat'l. code				surface	tolerance	projection	product family
Itr	ecn	no	dr	ASME Y14.5	ASME Y14.5		TERMINAL BLOCK
				tolerances unless otherwise specified			
				angles	X.±0.5		
				dr	X.X±0.3	MM	
				engr	X.X±0.1		
				chr	XX.X±0.1	scale	
				appd	XX.X±0.1		
				dr	HANKE FENG	032814	
				engr	HANKE FENG	032814	
				chr	SHI JUN	032814	
				appd	SHI JUN	032814	
sheet	revision	A					
index	sheet	1					



PDS: Rev :A 3

STATUS:Released

Printed: Jun 12,2014