


SK11221

THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO POSITRONIC AND IT'S SUBSIDIARIES. POSITRONIC BELIEVES THE DATA ON THIS DRAWING TO BE RELIABLE, SINCE THE TECHNICAL INFORMATION IS GIVEN FREE OF CHARGE, THE USER EMPLOYS SUCH INFORMATION AT HIS OWN DISCRETION AND RISK. POSITRONIC ASSUMES NO RESPONSIBILITY FOR RESULTS OBTAINED OR DAMAGES INCURRED FROM USE OF SUCH INFORMATION IN WHOLE OR IN PART.

DATE	REV	REVISION RECORD	APP	DR	CK
12-09-09	NC	ECO 31834	COLE	BS	COLE







NOTES:
1. MATERIALS AND FINISHES:
   INSULATOR: GLASS-FILLED DAP PER ASTM-D-5948, TYPE SDG-F, COLOR GRAY.
   CONTACTS: COPPER ALLOY, 0.000010 [0.25µ] GOLD OVER NICKEL FINISH.
2. ELECTRICAL CHARACTERISTICS:
   CONTACT CURRENT RATING: 7.5 AMPS, MAXIMUM.
   INITIAL CONTACT RESISTANCE: 0.010 OHMS, MAXIMUM.
   INSULATION RESISTANCE: 5 G OHMS, MINIMUM.
   WORKING VOLTAGE: 300 VAC [rms].
3. TEMPERATURE RANGE: -55°C TO +125°C.
4. DIMENSIONS ARE IN INCHES [MILLIMETERS].

POSITRONIC INDUSTRIES INC.
www.connectpositronic.com
FSCM 28198

DECIMAL TOL. ± 0.015 [0.38]	GF SERIES	SCALE N.T.S.	DRAWN BY B SHELLEDY
			APPROVED BY S COLE
	TITLE GF3F1MDSCL		
ANGULAR TOL. ± 5°	DATE 12-09-09	DRAWING NUMBER SK11221	REV. NC

Downloaded from Arrow.com.