




HONEYWELL
PART NUMBER
4

REV	DOCUMENT	CHANGED BY	CHECK
A	0016321	LKM 24OCT05	VA




POS1 POS2 POS3





NUMBER OF POLES
(1=SP-SINGLE POLE, USES TERMINALS 1-2-3)
(2=DP-DOUBLE POLE, USES TERMINALS 1-2-3 AND 4-5-6)

CIRCUITRY 5

TERMINAL STYLE



.250 WIDE QUICK
CONNECT TABS



MOUNTING HOLE
PANEL THICKNESS
(SNAP-IN BRACKET)
.030 MIN - .187 MAX
[.76] [4.75]

(A=AMBER, G=GREEN, R=RED, N=NONE)

(A=AMBER, G=GREEN, R=RED, N=NONE)

LAMP 7

LAMP 8

LED VOLTAGE
(2=6V, 3=12V, 4=24V)

ACTUATOR COLOR
(B=BLACK, G=GRAY, R=RED, W=WHITE)

BASE/BEZEL COLOR
(B=BLACK, G=GRAY, W=WHITE)


LENS STYLE AND COLOR 7
8 = WHITE TRANSLUCENT BAR
9 = WHITE TRANSLUCENT SQUARE
N=NONE

LENS STYLE AND COLOR 8
8 = WHITE TRANSLUCENT BAR
9 = WHITE TRANSLUCENT SQUARE
N=NONE

ELECTRICAL RATINGS
AND APPROVALS

10A 250VAC 1/2HP
15A 125VAC 1/2HP
UL, CSA

	CIRCUIT MADE WITH ROCKER IN 5		
	POSITION 3 (1&2, 4&5)	POSITION 2	POSITION 1 (2&3, 5&6)
1	ON	OFF	ON
2	OFF	NONE	ON
3	ON	NONE	ON
4	(OFF)	NONE	ON
5	(ON)	OFF	ON
6	OFF	NONE	(ON)
7	(ON)	OFF	(ON)
8	(ON)	NONE	ON



ILLUMINATION CIRCUIT DIAGRAMS 9

- 1 - OPERATING TEMPERATURE RANGE : -40°F TO +185°F (-40°C TO +85°C)
- 2 - ELECTRICAL LIFE : 50,000 CYCLES MOMENTARY, 100,000 CYCLES MAINTAINED
- 3 - MECHANICAL LIFE : 150,000 CYCLES MIN
- 4 - SEE DIAGRAM FOR CATALOGING SCHEME
- 5 - PARENTHESIS DENOTE MOMENTARY ACTION
- 6 - SEALED TO IP68
- 7 - ABOVE TERMINALS 1 AND 4
- 8 - ABOVE TERMINALS 3 AND 6
- 9 - REFER TO CIRCUIT DIAGRAMS

DESIGN UNITS: INCH		DRAWN	TSG	14 JUL 05	Honeywell			
TOLERANCES UNLESS NOTED:		CHECK	-	-				
NO PLACE	X ±	THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE			
ONE PLACE	.X ±	INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SWITCH , ROCKER			
TWO PLACE	.XX ±	Pro/ENGINEER 2D			SIZE	TYPE	DRAWING NAME	REV
THREE PLACE	.XXX ±				B	I	SRL SERIES CHART 1	A
FOUR PLACE	.XXXX ±				SCALE	-	SHEET	1 OF 1
ANGLES	X ±							

THIRD ANGLE PROJECTION

