Part Number : 314023100
Product Description : 2.54mm MX64 Sealed Single Row Crimp Housing, GET Terminal, Black, 3 Circuits, Key A, without CPA Lock
Series Number : 31402
Status : Active
Product Category : Connector Housings
Engineering Part Number : CVP-314023100



Documents and Resources

Drawings

314023100_sd.pdf

PK-31300-256-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

314020000-000.pdf

AS-31402-000-001.pdf

PS-31402-000-001.pdf

TS-31402-001-1X3-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Dodecamethylcyclohexasiloxane; Decamethylcyclopentasiloxane;

Downloaded from Arrow.com.

	Octamethylcyclotetrasiloxane per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	31402
Description	2.54mm MX64 Sealed Single Row Crimp Housing, GET Terminal, Black, 3 Circuits, Key A, without CPA Lock
Application	Power, Wire-to-Board
Product Name	MX64
UPC	822348285723

Physical

Circuits (maximum)	3
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes

Downloaded from Arrow.com.

Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	4.300/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Polarization	A
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +125°C

Solder Process Data

Lead-Free Process Capability	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	Sensors, Other USCAR Interfaces

Downloaded from Arrow.com.