
DATASHEET

SMD ▪ B
11-22/R6G6C-A31/2T



Features

- Package in 8mm tape on 7″ diameter reel.
- Compatible with automatic placement equipment.
- Compatible with infrared and vapor phase reflow solder process.
- Multi-color type.
- Pb-free.
- The product itself will remain within RoHS compliant version.
- Compliance with EU REACH.
- Compliance Halogen Free .(Br <900 ppm ,Cl <900 ppm , Br+Cl < 1500 ppm).

Description

- The 11-22 SMD LED is much smaller than lead frame type components, thus enable smaller board size, higher packing density, reduced storage space and finally smaller equipment to be obtained.
- Besides, lightweight makes them ideal for miniature applications. etc.

Applications

- Backlighting in dashboard and switch.
- Telecommunication: indicator and backlighting in telephone and fax.
- Flat backlight for LCD, switch and symbol.
- General use.

Copyright © 2010, Everlight All Rights Reserved. Release Date : Mar.16.2022Issue No: DSE-0013050 Rev.4

Ver.:4 Release Date:04/08/2022 狀態:Approved(正式發行)

Downloaded from Arrow.com.

Device Selection Guide

Code	Chip Materials	Emitted Color	Resin Color
R6	AlGaInP	Brilliant Red	Water Clear
G6	InGaN	Brilliant Yellow Green	

Absolute Maximum Ratings (Ta=25℃)

Parameter	Symbol	Code	Rating	Unit
Reverse Voltage	V_R		5	V
Forward Current	I_F	R6	25	mA
		G6	25	
Peak Forward Current (Duty 1/10 @1KHz)	I_{FP}	R6	60	mA
		G6	60	
Power Dissipation	Pd	R6	60	mW
		G6	60	
Electrostatic Discharge	ESD_{HBM}		2000	
Operating Temperature	T_{opr}		-40 ~ +85	℃
Storage Temperature	Tstg		-40 ~ +90	℃
Soldering Temperature	Tsol		Reflow Soldering : 260 ℃ for 10 sec. Hand Soldering : 350 ℃ for 3 sec.	

Copyright © 2010, Everlight All Rights Reserved. Release Date : Mar.16.2022Issue No: DSE-0013050 Rev.4

Ver.:4 Release Date:04/08/2022 狀態:Approved(正式發行)

Downloaded from Arrow.com.

Electro-Optical Characteristics (Ta=25℃)

Parameter	Symbol	Code	Min.	Typ.	Max.	Unit	Condition
Luminous Intensity	Iv	R6	285	-----	565	mcd	
		G6	112	-----	255		
Viewing Angle	$2\theta_{1/2}$		-----	60	-----	deg	
Peak Wavelength	λ p	R6	-----	632	-----	nm	
		G6	-----	575	-----		
Dominant Wavelength	λ d	R6	-----	624	-----	nm	I_F=20mA
		G6	-----	573	-----		
Spectrum Radiation Bandwidth	△ λ	R6	-----	20	-----	nm	
		G6	-----	20	-----		
Forward Voltage	V_F	R6	1.7	2.0	2.4	V	
		G6	1.7	2.0	2.4		
Reverse Current	I_R	R6	-----	-----	10	μA	V_R=5V
		G6	-----	-----	10		

Note:
1. Tolerance of Luminous Intensity: ±11%
2. Reverse Voltage(VR) Condition is applied to IR test only The device is not designed for reverse operation

Copyright © 2010, Everlight All Rights Reserved. Release Date : Mar.16.2022Issue No: DSE-0013050 Rev.4

Ver.:4 Release Date:04/08/2022 狀態:Approved(正式發行)

Downloaded from Arrow.com.

Bin Range of Luminous Intensity

R6

Bin Code	Min.	Max.	Unit	Condition
T1	285	360	mcd	I_F =20mA
T2	360	450		
U1	450	565		

G6

Bin Code	Min.	Max.	Unit	Condition
R1	112	140	mcd	I_F =20mA
R2	140	180		
S1	180	225		

EVERLIGHT


Copyright © 2010, Everlight All Rights Reserved. Release Date : Mar.16.2022Issue No: DSE-0013050 Rev.4


Ver.:4 Release Date:04/08/2022 狀態:Approved(正式發行)


Downloaded from Arrow.com.


Typical Electro-Optical Characteristics Curves


R6














Copyright © 2010, Everlight All Rights Reserved. Release Date : Mar.16.2022Issue No: DSE-0013050 Rev.4


Ver.:4 Release Date:04/08/2022 狀態:Approved(正式發行)

Downloaded from Arrow.com.


Typical Electro-Optical Characteristics Curves

G6


Spectrum Distribution




Forward Current vs. Forward Voltage




Luminous Intensity vs. Ambient Temperature




Luminous Intensity vs Forward Current



Forward Current Derating Curve



Radiation Diagram




Copyright © 2010, Everlight All Rights Reserved. Release Date : Mar.16.2022Issue No: DSE-0013050 Rev.4


Ver.:4 Release Date:04/08/2022 狀態:Approved(正式發行)

Downloaded from Arrow.com.


Package Dimension



TOP




Polarity




Side

Recommend soldering pad



Bottom



Suggested pad dimension is just for reference only.
Please modify the pad dimension based on individual need.


1. Note: Tolerances unless mentioned ±0.1mm. Unit = mm
2. No exposed circuit layer directly below the LED package to prevent short circuit.

Copyright © 2010, Everlight All Rights Reserved. Release Date : Mar.16.2022Issue No: DSE-0013050 Rev.4

Ver.:4 Release Date:04/08/2022 狀態:Approved(正式發行)


Downloaded from Arrow.com.

Moisture Resistant Packing Materials Label Explanation



- CPN: Customer's Product Number
- P/N: Product Number
- QTY: Packing Quantity
- CAT: Luminous Intensity Rank
- HUE: Chromaticity Coordinates & Dom. Wavelength Rank
- REF: Forward Voltage Rank
- LOT No: Lot Number

Reel Dimensions




Note: The tolerances unless mentioned is ±0.1mm ,Unit = mm

Copyright © 2010, Everlight All Rights Reserved. Release Date : Mar.16.2022Issue No: DSE-0013050 Rev.4

Ver.:4 Release Date:04/08/2022 狀態:Approved(正式發行)


Downloaded from Arrow.com.

Carrier Tape Dimensions: Loaded quantity 2000 PCS per reel



Note: The tolerances unless mentioned is ±0.1mm ,Unit = mm


Moisture Resistant Packaging




Copyright © 2010, Everlight All Rights Reserved. Release Date : Mar.16.2022Issue No: DSE-0013050 Rev.4
www.everlight.com
Ver.:4 Release Date:04/08/2022 狀態:Approved(正式發行)
Downloaded from Arrow.com.

Precautions For Use

1. Over-current-proof
   Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change (Burn out will happen).
2. Storage
   2.1 Do not open moisture proof bag before the products are ready to use.
   2.2 After opening the package: The LEDs should be kept at 30℃ or less and 60%RH or less.
   2.3 The LEDs should be used within 168 hours (7days) after opening the package .
   If unused LEDs remain, it should be stored in moisture proof packages.
   2.4 If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions.
   Baking treatment : 60±5℃ for 24 hours.
3. Soldering Condition
   3.1 Pb-free solder temperature profile



   3.2 Reflow soldering should not be done more than two times.
   3.3 When soldering, do not put stress on the LEDs during heating.
   3.4 After soldering, do not warp the circuit board.
4. Soldering Iron
   Each terminal is to go to the tip of soldering iron temperature less than 350℃ for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.
5. Repairing
   Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.



Copyright © 2010, Everlight All Rights Reserved. Release Date : Mar.16.2022Issue No: DSE-0013050 Rev.4

Ver.:4 Release Date:04/08/2022 狀態:Approved(正式發行)
Downloaded from Arrow.com.

Application Restrictions

High reliability applications such as military/aerospace, automotive safety/security systems, and medical equipment may require different product. If you have any concerns, please contact Everlight before using this product in your application. This specification guarantees the quality and performance of the product as an individual component. Do not use this product beyond the specification described in this document.

Copyright © 2010, Everlight All Rights Reserved. Release Date : Mar.16.2022Issue No: DSE-0013050 Rev.4

Ver.:4 Release Date:04/08/2022 狀態:Approved(正式發行)

Downloaded from Arrow.com.

DISCLAIMER

1.EVERLIGHT reserves the right(s) on the adjustment of product material mix for the specification.
2.The product meets EVERLIGHT published specification for a period of twelve (12) months from date of shipment.
3.The graphs shown in this datasheet are representing typical data only and do not show guaranteed values.
4.When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from the use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
5.These specification sheets include materials protected under copyright of EVERLIGHT. Reproduction in any form is prohibited without obtaining EVERLIGHT's prior consent.
6.This product is not intended to be used for military, aircraft, automotive, medical, life sustaining or life saving applications or any other application which can result in human injury or death. Please contact authorized Everlight sales agent for special application request.

Copyright © 2010, Everlight All Rights Reserved. Release Date : Mar.16.2022Issue No: DSE-0013050 Rev.4

Ver.:4 Release Date:04/08/2022 狀態:Approved(正式發行)

Downloaded from Arrow.com.