




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: .51 – 1.65 mm²

Mating Tab Width: 4.75 mm [.187 in]

Mating Tab Thickness: .81 mm [.032 in]

Features

Product Type Features

Insertion Force	Normal
-----------------	--------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Electrical Characteristics

Voltage Rating	250 V
----------------	-------

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	4.75 mm [.187 in]
Mating Tab Thickness	.81 mm [.032 in]
Terminal Orientation	Straight
Contact Base Material	Phosphor Bronze
Terminal Plating Material	Pre-Tin
Crimp Type	F-Crimp



Barrel Type	Open
-------------	------

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Locking Lance Height	1.2 mm
----------------------	--------

Wire Insulation Support	With
-------------------------	------

Mating Retention Type	Locking Lance
-----------------------	---------------

Extraction Force	4 Newton
------------------	----------

Dimensions

Product Length	16 mm [.629 in]
----------------	-----------------

Compatible Insulation Diameter Range	2.31 – 3.3 mm [.091 – .129 in]
--------------------------------------	--------------------------------

Terminal Material Thickness	.25 mm [.01 in]
-----------------------------	-----------------

Wire Size	.51 – 1.65 mm ²
-----------	----------------------------

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Operating Temperature Range	-40 – 110 °C [-40 – 230 °F]
-----------------------------	-----------------------------

Packaging Features

Packaging Quantity	8000
--------------------	------

Packaging Method	Strip/Reel
------------------	------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
--	---

Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	--

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2150309-1
OCEAN_2.0_APPLICATOR-E-090F130F-REM



KIT
REPRESENTATION ONLY

TE Part # 7-2150309-7
OCEAN_2.0_SPARE_PART_KIT-090F130F



TE Part # 2150309-2
OCEAN_2.0_APPLICATOR-E-090F130F-REA




TE Part # 281197-6
FF 187 REC 1.0-2.5MM2 PTBR




TE Part # 281197-5
FF 187 REC 1.0-2.5MM2 PTBR (RE REELING)


Also in the Series | FASTIN-FASTON 187




Automotive Housings(1)



Crimp Terminal Housings(3)



Insertion & Extraction Tools(1)



Quick Disconnects(20)

Customers Also Bought



TE Part #CAT-J6A-XCC
XRC Connector Contacts



TE Part #1-180907-6
FF 250 REC HSG 2P NYLON NAT



TE Part #211161-1
SKT CONTACT ASSY



TE Part #4-640429-0
10P MTA156 CONN ASSY 24AWG
WHT



TE Part #4-640429-2
12P MTA156 CONN ASSY 24AWG
WHT



TE Part #1377173-5
SMP 0-0130102-0



TE Part #6-1393292-3
V23074A2002A403-EV-CBOX



TE Part #1-1904045-6
V23333Z0001B046-EV-100



TE Part #6-1904045-5
V23333Z1001B045-EV-441

Documents

Product Drawings

[FF 187 REC 0.5-1.5MM2 TPPB](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_280919-4_M.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_280919-4_M.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_280919-4_M.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



[FASTIN_FASTON_Product_Line](#)

English

Product Specifications

[Application Specification](#)

[FASTIN-FASTON Connector, .187 rec. etc.](#)