

4

3




2

1

used for:

D-SUB

POS.	A -0.76	B -0.25	C	Part-No.
9	31.19	16.46	25.00 $+0.12$ -0.13	320X12519X
15	39.52	24.79	33.30 $+0.15$ -0.1	320X12539X
25	53.42	38.50	47.04 ± 0.13	320X10559X
37	69.70	54.96	63.50 ± 0.13	320X12559X



NOTES:

1. METALSHELLS: STEEL; min. 320 pin TIN

2. INSULATORS: PBT GF UL 94 V-0, BLUE

3. CONTACTS: COPPER ALLOY,

(b) PLATING: GOLD FLASH over NICKEL

4. MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB


5. CONNECTOR IS PART MARKED: PART-NO. CONEC ABC

(b) 6. CURRENT RATING: 1,5 A

(b) 7. OPERATING TEMPERATURE: -25 °C ... +85 °C

RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

				tolerance		 dim. in mm
				2006	date	name
				drawn	03.02.	Lehmenkühler
				appd.	03.02.	Mickenbecker
				norm	DIN 41652	
				d-old		
3 x b	Ä21-0102	23.02.2022	ABU			
a	Original					
rev.	description	date	name			

dwg no:		AutoCAD 2004	DIN-A
16K1A1724		4	sh: 1/1
part no:		SEE TABLE	