



FEMALE PLUG M8 STRAIGHT



NOTES:
RATED VOLTAGE: 3 contacts 60V AC/DC
4 and 5 contacts 30V AC/DC
CURRENT RATING: 3, 4, 5 contacts 3A
PROTECTION CLASS: IP 67
TEMPERATURE: -25°C / +80°C
PACKAGING ACCORDING TO PACKAGING SPEC. 1201202000

CONTACTS POSITION FRONT VIEW:						
FEMALE	3 CONTACTS		4 CONTACTS		5 CONTACTS	
	PIN	WIRE	PIN	WIRE	PIN	WIRE
	1	BROWN	1	BROWN	1	BROWN
	3	BLUE	2	WHITE	2	WHITE
CONNECTIONS	4	BLACK	3	BLUE	3	BLUE
			4	BLACK	4	BLACK
					5	GREY
CODING ACCORDING TO IEC 61076-2-104						



FOR OPTIONS SEE - NUMERICAL CODE - ON SHEET 2

8	2	I/D CARRIER (SEE MATRIX)	---	---
7	1	LABEL YELLOW	VINYL	---
	-	PRINTING FOR CABLES lxx	---	---
6	-	CABLE	SEE SHEET 2	---
5	-	OVERMOULDING	TPU	SEE SHEET 2
4	1	COUPLING NUT M8 FEMALE	BRASS	SEE SHEET 2
3	1	INSERT FEMALE BLACK	TPU	---
2	1	O-RING RED	FKM	---
1	3 / 4 / 5	CONTACT M8 FEMALE	COPPER	SELECTIVE Au OVER Ni
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS		SCALE		CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS AS PER PCN #517562				molex M8 SINGLE ENDED FEMALE STRAIGHT PRODUCT CUSTOMER DRAWING	
mm		2:1							
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 842894 DRWN: PRANAA2025/12/10 CHK'D: GGA2025/12/24 APPR: GGA2025/12/24					
ANGULAR TOL ± 1.0 °									
4 PLACES		±							
3 PLACES		±							
2 PLACES		± 0.05		INITIAL REVISION: DRWN: AKONDRACIUKECNO: 842894 APPR: MIWASIECZKO2017/02/162017/11/16					
1 PLACE		± 0.3							
0 PLACES		± 0.5							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES	
						A3-SIZE		120086	

ENGINEERING NO. - NUMERICAL CODE

(Available parts see PART LIST table. Other parts available upon request).

OPTIONS

4

0

X

0

0

0

X

X

X

X

X

X

X

X

40=Nano-Change
M8x1
Double ended

Contacts:
3=3 Contacts
4=4 Contacts
5=5 Contacts

Heads style:
000=Plug Female Straight

Cable type: See Table

Units:
M=Meter
C=Centimeter




Length
Examples:
005=0.5 unit
010=1 unit
100=10 unit

Overmold color:
Blank (Standard) = Black
A = Grey / G = Black / Y = Yellow
For cables K03, K05, A09, S19,
S20, S26 & A10 = Yellow

Coupling Nut material:
Blank = Standard
1 = Stainless steel
2 = Nylon
3 = Nickel plated Brass
4 = Valox (polyester)
5 = Delrin
6 = clear anodized alum.
7 = Teflon coat
Blank = 7 for cables: I20, I26, K03, K05, P82, S26
8 = Type 316 stainless steel
9 = Knurled / Hexagonal SW9 Brass Ni Plated

H = 2 pcs. of I/D Carrier PVC Transparent
(Cables lxx & P82 always with 2 pcs. of
I/D Carrier)

COUPLING NUT
FEMALE



CABLE INFORMATION

(for more information see Cable Data Sheet).

CABLE TYPE	NO. OF WIRES	CROSS SECTION	CABLE JACKET	UL	CSA	STATIC: TEMP. / BENDING RADIUS	DYNAMIC: TEMP. / BENDING RADIUS	DRAG CHAIN	SHIELD
E02	3 / 4 / 5	0.25mm²	PVC BLACK	UL 2464/1729	C22.2 I/II A/B 80°C/300V	-30°C to +80°C, >10xO.D.	-10°C to +80°C, >15xO.D.	-	-
E18	3 / 4	0.20mm²	PVC YELLOW	-	-	-30°C to +70°C	-5°C to +70°C	-	-
E51	4	0.25mm²	PVC GREY	-	-	-	-	-	-
E52	3 / 4 / 8	0.34mm²	PVC GREY	-	-	-30°C to +70°C	-5°C to +70°C	-	-
E54	3	0.25mm²	PVC GREY	-	-	-25°C to +70°C	-5°C to +70°C	-	-
H08	3 / 4 / 5	0.25mm²	PUR BLACK LS0H	UL 21198/10493	C22.2 I/II A/B 80°C/300V	-40°C to +80°C, >5xO.D.	-25°C to +80°C, >10xO.D.	2 000 000 cycles at 20°C, Temp. range +5°C to +60°C	-
H09	3 / 4 / 5	0.34mm²	PUR BLACK LS0H	UL 21198/10493	C22.2 I/II A/B 80°C/300V	-40°C to +80°C, >5xO.D.	-25°C to +80°C, >10xO.D.	2 000 000 cycles at 20°C, Temp. range +5°C to +60°C	-
H69	4	0.20mm²	PUR GRAY LS0H	-	-	-	-	-	-
I02	3 / 4	0.25mm²	PVC CEI GREY	-	-	-30°C to +70°C	-5°C to +70°C	-	-
P02	3 / 4 / 5	0.25mm²	PUR / PVC BLACK	-	-	-30°C to +80°C, >7xO.D.	-5°C to +80°C, >15xO.D.	-	-
P03	3 / 4 / 5	0.34mm²	PUR / PVC BLACK	-	-	-30°C to +80°C, >7xO.D.	-5°C to +80°C, >15xO.D.	-	-
P18	4	0.20mm²	PUR YELLOW	-	-	-	-	-	-
P82	3	0.34mm²	PUR IRR ORANGE	-	-	-50°C to +105°C, >5xO.D.	-40°C to +105°C, >7.5xO.D.	-	-
K05	3 / 4 / 5	0.34mm²	TPE YELLOW	UL ITC E195601 or PLC	I/II A/B 90°C/300V	-	-	-	-
L03	3	0.34mm²	Blend PUR ORANGE	-	-	-30°C to +90°C	-5°C to +90°C	-	-
A10	3 / 4 / 5	0.25mm²	PVC YELLOW	UL 2661	I/II A/B 105°C/300V	-	-	-	-

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS

mm

SCALE

2:1

GENERAL TOLERANCES
(UNLESS SPECIFIED)

ANGULAR TOL ± 1.0 °

4 PLACES ±

3 PLACES ±

2 PLACES ± 0.05

1 PLACE ± 0.3

0 PLACES ± 0.5

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

CURRENT REV DESC: REMOVED OBSOLETE PART
NUMBERS AS PER PCN #517562

EC NO: 842894
DRWN: PRANAA
CHK'D: GGA
APPR: GGA

INITIAL REVISION:
DRWN: AKONDRACIUK
APPR: MIWASIECZKO

THIRD ANGLE PROJECTION

DRAWING

SERIES

MATERIAL NUMBER

CUSTOMER

SHEET NUMBER

2025/12/10

2025/12/24

2025/12/24

2017/02/16

2017/11/16

A3-SIZE

120086

SEE PART LIST

GENERAL MARKET

2 OF 4

molex

M8 SINGLE ENDED FEMALE STRAIGHT

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER

1200860594

DOC TYPE

PSD

DOC PART

000

REVISION

A12

PART LIST

Pos.	Part. No	Engineering No.	Cable Length	Pos.	Part. No	Engineering No.	Cable Length	Pos.	Part. No	Engineering No.	Cable Length	Pos.	Part. No	Engineering No.	Cable Length
1	1200270066	403000E02M020	2m	36	1200868266	403000E02M045	4.5m	71	1200271409	403000H08M010	1m	106	1200868275	403000P02M002	0.2m
2	1200270067	403000E02M030	3m	37	1200868267	403000E02M0501	5m	72	1200271442	403000H08M020G	2m	107	1200868276	403000P02M002G	0.2m
3	1200270068	403000E02M050	5m	38	1200868268	403000E02M060	6m	73	1200868045	403000H08M020	2m	108	1200868277	403000P02M003	0.3m
4	1200270070	403000E02M100	10m	39	1200868339	404000E02C200	2m	74	1200868053	404000H08M050	5m	109	1200868278	403000P02M003G	0.3m
5	1200270127	404000E02M020	2m	40	1200868340	404000E02M015	1.5m	75	1200868060	404000H08M030	3m	110	1200868279	403000P02M005	0.5m
6	1200270129	404000E02M050	5m	41	1200868341	404000E02M0201	2m	76	1200868101	403000H08M050	5m	111	1200868280	403000P02M006	0.6m
7	1200270131	404000E02M100	10m	42	1200868342	404000E02M040	4m	77	1200868115	403000H08M100	10m	112	1200868281	403000P02M010	1m
8	1200270132	404000E02M150	15m	43	1200868343	404000E02M0501	5m	78	1200868116	403000H08M200	20m	113	1200868282	403000P02M012	1.2m
9	1200270133	404000E02M200	20m	44	1200868344	404000E02M080	8m	79	1200868117	404000H08M100	10m	114	1200868283	403000P02M018	1.8m
10	1200270400	403000E02M010	1m	45	1200868345	404000E02M110	11m	80	1200868118	404000H08M200	20m	115	1200868284	403000P02M022	2.2m
11	1200270549	404000E02M010	1m	46	1200868346	404000E02M170	17m	81	1200868122	403000H08M030	3m	116	1200868285	403000P02M030	3m
12	1200271410	403000E02M012	1.2m	47	1200868347	404000E02M210	21m	82	1200868162	404000H08M040	4m	117	1200868286	403000P02M032	3.2m
13	1200271417	403000E02M006	0.6m	48	1200868348	404000E02M250	25m	83	1200868207	404000H08M020	2m	118	1200868287	403000P02M035	3.5m
14	1200271418	403000E02M015	1.5m	49	1200868423	403000E02M1001	10m	84	1200868209	403000H08M015	1.5m	119	1200868288	403000P02M040	4m
15	1200271419	403000E02M025	2.5m	50	1200868442	403000E02M020Y	2m	85	1200868214	403000H08M005	0.5m	120	1200868289	403000P02M050G	5m
16	1200271423	404000E02M005	0.5m	51	1200868443	403000E02M050Y	5m	86	1200868215	404000H08M005	0.5m	121	1200868290	403000P02M055	5.5m
17	1200865038	403000E02M250	25m	52	1200868444	403000E02M100Y	10m	87	1200868395	405000H08M020	2m	122	1200868291	403000P02M080	8m
18	1200868015	403000E02M200	20m	53	1200868452	404000E02M050Y	5m	88	1200868404	405000H08M050	5m	123	1200868292	403000P02M150	15m
19	1200868067	404000E02M050G	5m	54	1200868453	404000E02M100Y	10m	89	1200868405	405000H08M100	10m	124	1200868351	404000P02M003	0.3m
20	1200868068	404000E02M100G	10m	55	1200868454	404000E02M150Y	15m	90	1200868468	403000H08M050Y	5m	125	1200868352	404000P02M030	3m
21	1200868069	404000E02M200G	20m	56	1200868467	403000E02M150Y	15m	91	1200868469	403000H08M100Y	10m	126	1200868353	404000P02M040	4m
22	1200868070	404000E02M300G	30m	57	1200868473	404000E02M1001	10m	92	1200868487	404000H08M010	1m	127	1200868354	404000P02M070	7m
23	1200868071	404000E02M400G	40m	58	1200868508	404000E02M050H	5m	93	1200868596	403000H08M010Y	1m	128	1200868355	404000P02M500	50m
24	1200868075	404000E02M020G	2m	59	1200868509	404000E02M100H	10m	94	1200868476	403000H09M020	2m	129	1200868517	403000P02M200	20m
25	1200868090	403000E02M150	15m	60	1200868510	404000E02M150H	15m	95	1200270709	405000P02M020	2m	130	1200868530	404000P02M010	1m
26	1200868099	405000E02M020	2m	61	1200868511	404000E02M030H	3m	96	1200860475	405000P02M050	5m	131	1200868627	405000P02M050Y	5m
27	1200868109	403000E02M100G	10m	62	1200868518	404000E02C230	2.3m	97	1200860594	405000P02M100	10m	132	1200868773	404000P02M060	6m
28	1200868114	404000E02M030	3m	63	1200868571	405000E02M120	12m	98	1200868001	403000P02M020	2m	133	1200868775	404000P02M200	20m
29	1200868151	405000E02M040	4m	64	1200868572	405000E02M030	3m	99	1200868002	403000P02M050	5m	134	1200860340	403000K05M050	5m
30	1200868171	405000E02M050	5m	65	1200868685	403000E02M050H	5m	100	1200868003	403000P02M100	10m	135	1200868431	403000K05M150	15m
31	1200868172	405000E02M100	10m	66	1200868696	404000E02M0509H	5m	101	1200868148	405000P02M005	0.5m	136	1200270642	403000L03M005A	0.5m
32	1200868262	403000E02M002	0.2m	67	1200868697	404000E02M1009H	10m	102	1200868156	404000P02M020	2m	137	1200270080	403000I02M003	0.3m
33	1200868263	403000E02M003	0.3m	68	1200868698	404000E02M1509H	15m	103	1200868157	404000P02M050	5m	138	1200270081	403000I02M020	2m
34	1200868264	403000E02M020H	2m	69	1200868774	404000E02M060	6m	104	1200868158	404000P02M100	10m	139	1200270082	403000I02M030	3m
35	1200868265	403000E02M035	3.5m	70	1200868776	404000E02M070	7m	105	1200868274	403000P02C350	3.5m	140	1200270083	403000I02M050	5m

CABLE LENGTH TOLERANCES		
OVER [mm]	UP TO AND INCLUDING [mm]	TOLERANCES [mm]
0	305	+19
305	915	+45
915	1830	+56
1830	3660	+89
3660	7320	+165
7320	14640	+317
14640	30500	+610
30500	>	+2% OF FINISHED LENGTH

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS

SCALE

mm

2:1

GENERAL TOLERANCES (UNLESS SPECIFIED)

ANGULAR TOL

±

1.0 °

4 PLACES

±

3 PLACES

±

2 PLACES

±

0.05

1 PLACE

±

0.3

0 PLACES

±

0.5

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

THIRD ANGLE PROJECTION

DRAWING

SERIES

MATERIAL NUMBER

CUSTOMER

SHEET NUMBER

CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS AS PER PCN #517562

EC NO: 842894

DRWN: PRANAA

CHK'D: GGA

APPR: GGA

INITIAL REVISION:

DRWN: AKONDRACIUK

APPR: MIWASIECZKO

2025/12/10

2025/12/24

2025/12/24

2017/02/16

2017/11/16

M8 SINGLE ENDED FEMALE STRAIGHT

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER

1200860594

DOC TYPE

PSD

DOC PART

000

REVISION

A12

SEE PART LIST


GENERAL MARKET

3 OF 4

PART LIST

Pos.	Part. No	Engineering No	Cable Length
141	1200270084	403000I02M100	10m
142	1200270148	404000I02M020	2m
143	1200270149	404000I02M050	5m
144	1200270360	404000I02M100	10m
145	1200860041	404000I02M030	3m
146	1200868269	403000I02M005	0.5m
147	1200868270	403000I02M006	0.6m
148	1200868271	403000I02M010	1m
149	1200868272	403000I02M025	2.5m
150	1200868273	403000I02M150	15m
151	1200868349	404000I02M003	0.3m
152	1200868445	403000I02M030Y	3m
153	1200868446	403000I02M050Y	5m
154	1200868447	403000I02M100Y	10m
155	1200868455	404000I02M020Y	2m
156	1200868456	404000I02M050Y	5m
157	1200868460	404000I02M100Y	10m
158	1200868507	403000I02M020Y	2m
159	1200868566	404000I02M030Y	3m
163	1200868192	403000P82M0207	2m
169	1200271449	403000P18M070	7m
170	1200860102	403000A10M020	2m
171	1200860107	403000A10M050	5m
172	1200860111	403000A10M100	10m
173	1200860112	403000A10M150	15m
174	1200860144	404000A10M020	2m
175	1200860145	404000A10M030	3m

Pos.	Part. No	Engineering No	Cable Length
176	1200860147	404000A10M050	5m
177	1200860155	404000A10M100	10m
178	1200860191	405000A10M020	2m
179	1200270140	404000E18M050	5m
181	1200270606	403000E18M100	10m
182	1200860667	405000P02M200	20m
183	1200868849	405000H08M010	1m
184	1200868857	405000E02M010	1m
185	1200868934	404000H08M050H	5m
186	1200869026	404000H09M005	0.5m
187			
188			
189			
190			
191			
192			
193			
194			
195			
196			
197			
198			
199			
200			
201			
202			
203			
204			
205			
206			
207			
208			
209			
210			

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS mm		SCALE 1:1		CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS AS PER PCN #517562			molex		
GENERAL TOLERANCES (UNLESS SPECIFIED)									
ANGULAR TOL ± 1.0 °							M8 SINGLE ENDED FEMALE STRAIGHT		
4 PLACES		±							
3 PLACES		±		2025/12/10			PRODUCT CUSTOMER DRAWING		
2 PLACES		± 0.05							
1 PLACE		± 0.3		2025/12/24			DOCUMENT NUMBER 1200860594		
0 PLACES		± 0.5							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				EC NO: 842894 DRWN: PRANAA CHK'D: GGA APPR: GGA			2025/12/10 2025/12/24 2025/12/24		
INITIAL REVISION: DRWN: AKONDRACIUK APPR: MIWASIECZKO				2017/02/16 2017/11/16			DOC TYPE DOC PART REVISION PSD 000 A12		
THIRD ANGLE PROJECTION 		DRAWING A3-SIZE		SERIES 120086		MATERIAL NUMBER SEE PART LIST		CUSTOMER GENERAL MARKET	
								SHEET NUMBER 4 OF 4	