




1719040-1 Product Details

Share Print Email



Active
View 3D PDF

GET 0.64 mm (Global Electronic Technology) Connector System

8POS GET MALE CONNECTOR W. 3 SB'S

1719040-1

TE Internal Number: 1719040-1

Product Highlights View All

- GET 0.64 Product Line
- Connector
- Wire-to-Wire
- Contact Type = Pin
- Housing

Pricing & Availability

Request Sample

Add to My Part List

Buy Product through Distributor

Documents

Features

Compliance

Please Note:
Use the Product Drawing for all design activity

Product Type Features	
Product Line	GET 0.64
Product Type	Connector
Connector Type	Housing
Sealed	No
Wire/Cable Type	Discrete Wire

Mechanical Attachment	
Contact Retention Type	Orientation Bump
Mating Retention Type	Latch(ing)

Electrical Characteristics	
Contact - Rated Current (A)	3 – 8

Termination Features	
Termination Method to Wire/Cable	Crimp
Wire/Cable Size (mm²)	0.22 – 0.75
Wire/Cable Size (AWG)	18 – 22

Dimensions	
Length (X-Axis) (mm [in])	37.20 [1.464]
Width (Z-Axis) (mm [in])	26.20 [1.0314]
Profile Height (Y-Axis) (mm [in])	18.80 [0.740]

Body Features	
Wire Type	Stranded
Assembly Integration Feature	With
Assembly Integration Type	TPA (Terminal Position Assurance)

Contact Features	
Contact Type	Pin

Housing Features	
Connector Style	Plug
Housing Material	PA66 GF35
Centerline (mm [in])	2.54 [0.100]
Housing Color	Yellow
Mating Alignment	With
Mating Alignment Type	Keyed

Configuration Features	
Number of Rows	1 x 8
Number of Positions	8
Keying Arrangement	X
Shorting Bar	With
Number of Shunts/Shorting Bars	3
Number of Positions, Shunt(s) Applied	6
GET 0.64 Connector System	Yes

Industry Standards	
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant

Conditions for Usage	
Applies To	Wire/Cable
Accepts Wire Insulation Diameter, Range (mm [in])	1.10 – 2.06 [0.043 – 0.0811]

Operation/Application	
Application Use	Wire-to-Wire
Contact Transmits (Typical Application)	Signal

Packaging Features	
Packaging Method	Box/Carton
Packaging Quantity	600

Other	
Brand	TE Connectivity

Related Products

Not quite the product you're looking for?

Find Similar Products

View Part in Product Feature Selector

Check for Tooling

Corporate Information

About TE
Investors
News Room
Supplier Portal
Careers
Terms of Use of TE.com
Privacy Policy
Global Accessibility Statement

Quick Links

Distributor Inventory
Product Cross Reference
Documents & Drawings
Product Compliance Support Center
Site Map
Terms & Conditions of Sale

Customer Support

Email or Chat With Us
Find a Phone Number
Knowledge Base
Manage Your Account

Keep Me Informed

