

POLARIZATION CHART			
KEYING LETTER	F DEGREES	G DEGREES	H DEGREES
T	100°	150°	110°
U	120°	130°	110°
V	115°	130°	115°
W	125°	110°	125°
X	130°	100°	130°
Y	110°	140°	110°
Z	100°	160°	100°
S	135°	135°	90 °
NONE	120°	120°	120°


DATA CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO TROMPETER ELECTRONICS INC. AND SHALL NOT BE DISCLOSED, COPIED OR USED FOR PROCUREMENT OR MANUFACTURE WITHOUT EXPRESS WRITTEN PERMISSION OF TROMPETER ELECTRONICS INC.


REVISIONS		3-0002	SH 1
REV	DESCRIPTION	DATE	APPROVED
P	REVISED PER ECO 15112	7/10/03	WJ

RED INDICATES ORIGINAL










RECOMMENDED
PANEL CUTOUT
SCALE: 2/1



SCHEMATIC

5. EXAMPLE OF COMPLETE MODEL NO:

BJ78 Y

BASIC MODEL NO — KEY LTR (POLARIZATION)

4. CONCENTRIC TWINAX/TRIAX TRB
   BULKHEAD MOUNT FEEDTHRU RECEPTACLE
3. MAX PANEL THK .187
2. FINISH: TFS-1A (NICKEL)
1. ALL DIM ARE IN INCHES

INTERPRET DRAWING PER MIL-STD-100
DIMENSIONS ARE IN INCHES
AND INCLUDE FINISH THICKNESS
UNLESS OTHERWISE SPECIFIED

DRAWN	AAH 7-7-03
CHECKED	JZM 7-8-03
QUALITY	7/10/03
MFG	7/10/03
APPROVED	7/10/03
NEXT ASSY	CAD FILE NO. 3-0002P

TOL: UNLESS SPECIFIED
.XX
.XXX ±.005
.XXXX
ANGLES
MATERIAL:
FINISH:
DO NOT SCALE DWG

TROMPETER RF connectivity
a cinch connectivity solutions brand

TITLE: BJ78

SIZE	CAGE CODE	DRAWING NO.	REV.
B	14949	3-0002	P

SCALE 4/1 DATE: 1-31-61 SHEET 1C

Downloaded from Arrow.com.

Please read our datasheet & drawing disclaimer here.