

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A

A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

BZ-2RW80225-A2**BZ-2RW80225-A2**

PAGE 1 OF 1

MDRAWING
NUMBER

4

ISSUE

REPLACES X66885 - BZ

PR - 6620

RELEASE NO.

CHECK

REVISIONS

A	CO-73287-B
B	CO-77589
C	CO93346

MAM
29 MAR 94DLT
2 SEP 98

CHECK

3 AUG 77

CEB

77 CHECK


3 AUG

KSW

DRAWN

FORMTEK


FO-52848-A



NOTE
MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON $1.000 \pm .002$ CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

**CHARACTERISTICS**

OPERATING FORCE --- 4 1/2 OZ MAX

RELEASE FORCE ----- 3/4 OZ MIN

DIFFERENTIAL TRAVEL --- .004-.030

OVERTRAVEL ----- .141 MIN

ELECTRICAL DATACONTACT ARRANGEMENT
S P D T

UL LISTED - FILE E12252
15A-125, 250 OR 480 VAC, 2A-600 VAC
1/8HP-125 VAC; 1/4HP-250 VAC
CODE L74 1/2A-125 VDC; 1/4A-250 VDC

L288

L299

L306



16A 250V ~ T85 5E4

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR
REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

	DIM. mm	TOL. mm/in	DIM. in	TOL. mm/in
NO PLACES	X	1/04	X	0.01
ONE PLACE	X,X	0.4/016	X,X	0.01/03
TWO PLACES	X,X,X	0.15/006	X,X,X	0.001/015
THREE PLACES	X,X,X,X		X,X,X,X	0.13/005

DESIGN UNITS

SI METRIC

US CUSTOMARY

WEIGHT .073 LB