

Commercial Space Line

InstaBend® 047

High Performance Microwave Assemblies

InstaBend® are flexible, coaxial microwave assemblies designed for interconnects between RF circuit cards, modules and enclosure panels. The cable can be bent very closely behind the connector, simplifying cable routing.

Features:

- Sold as cable assemblies
- Low outgassing materials per ASTM E595
- Class 100,000 clean room manufacturing
- Vented connectors, if applicable
- Optimized for lowest attenuation
- Ultra stable performance with flexure
- Superior shielding effectiveness (>90 dB)
- Radiation Resistance: 30 MRads

Specifications

Ω Impedance
50 Ohms

Op Temp
-85 to +257°F
-65 to +125°C

Units

Diameter	in (mm)	0.064 (1.63)
Weight	lb/ft (g/m)	0.004 (6)
Minimum Bend Radius	in (mm)	0.130 (3.30)
Maximum Frequency	GHz	50
Velocity of Propagation	%	70
Capacitance	pF/ft (pF/m)	29.9 (98.1)
Delay	ns/ft (ns/m)	1.45 (4.76)
Shielding	dB	>90

Calculation

$$IL = (K1 \times \sqrt{f} + K2 \times f) \times \text{Cable Length} + \text{Connector Loss}$$

Cable Insertion Loss
 f = Frequency (MHz)

Use K values with
matching length unit

K values	dB/ft	dB/m
K1	0.01195	0.03920795
K2	0.000013	0.000042653



CENTER CONDUCTOR

Silver Plated Copper
Clad Steel

DIELECTRIC

PTFE

SHIELD

Silver Plated Copper
Clad Steel

OUTER BRAID

Silver Plated Copper
Clad Steel

JACKET

Blue FEP

Insertion loss & VSWR

Stock Code	Max. Insertion Loss in dB @ 40GHz	Max. VSWR @ 40GHz
IE-00414-01	1.53	1.40
IE-00414-02	2.07	1.40
IE-00414-03	2.60	1.40
IE-00414-04	3.13	1.40
IE-00414-05	3.67	1.40
	Max. Insertion Loss in dB @ 22GHz	Max. VSWR @ 22GHz
IE-00415-01	1.10	1.35
IE-00415-02	1.48	1.35
IE-00415-03	1.85	1.35
IE-00415-04	2.23	1.35
IE-00415-05	2.61	1.35


Times Microwave Systems
358 Hall Avenue, Wallingford, CT 06492, USA
T 800. 867.2629
www.timesmicrowave.com

TIMES
MICROWAVE SYSTEMS
AN AMPHENOL COMPANY

InstaBend® 047


High Performance Microwave Assemblies

Ordering Guide



Stock Code	Part-Number	Length (L) in inch
IE-00414-01	IBS047-KMKM-4.0IN	4
IE-00414-02	IBS047-KMKM-6.0IN	6
IE-00414-03	IBS047-KMKM-8.0IN	8
IE-00414-04	IBS047-KMKM-10.0IN	10
IE-00414-05	IBS047-KMKM-12.0IN	12

Connector Code	Description	Connector Body	Center Contact	Connector Loss (per pair)
SP121	Type K (M) Straight	Stainless Steel, Gold Plated	Beryllium Copper, Gold Plated	0.06 x v(f) (GHz)



Stock Code	Part-Number	Length (L) in inch
IE-00415-01	IBS047-SMSM-4.0IN	4
IE-00415-02	IBS047-SMSM-6.0IN	6
IE-00415-03	IBS047-SMSM-8.0IN	8
IE-00415-04	IBS047-SMSM-10.0IN	100
IE-00415-05	IBS047-SMSM-12.0IN	12

Connector Code	Description	Connector Body	Center Contact	Connector Loss (per pair)
SP112	Type SMA (M) Straight	Stainless Steel, Gold Plated	Beryllium Copper, Gold Plated	0.06 x v(f) (GHz)



Global manufacturing capability: US, and Asia.



Heritage—in the air and on the ground, thousands of assemblies built over decades.



Assembled and tested assemblies provide assured performance.

Rev.3: 3/27/2023

Times Microwave Systems
 358 Hall Avenue, Wallingford, CT 06492, USA
 T 800. 867.2629
www.timesmicrowave.com