




KA2U, AL Set Screw Terminal, Dual Rated, 1-Hole

By Burndy
Catalog # [KA2U](#)

Aluminum Universal Terminal, 1 Hole, 14-2 AWG (Str), 1/4" Stud, 1 Screw, Al/Cu Rated, Tin Plated



Features

- Dual Rated Panelboard Lugs
- High strength extruded aluminum alloy
- Electro tin-plated for low contact resistance
- Rated to 35kV

Application

For Aluminum And Copper Conductors

Specifications

Buy American Compliant	Contact Manufacturer
EU RoHS Indicator	Yes
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Nominal Diameter	0.072, 0.091, 0.116, 0.130, 0.146, 0.164, 0.184, 0.184, 0.184, 0.184, 0.184, 0.206, 0.232, 0.232, 0.260, 0.260, 0.292, 0.320
Conductor - AL Str Size	<ul style="list-style-type: none"> • 8 • 6 • 4 • 3 • 2
Conductor - AL Str Size Range	8-2
Conductor - Copper Str Size	<ul style="list-style-type: none"> • 14 • 12 • 10 • 9 • 8 • 7 • 6 • 5 • 4 • 3

Conductor Size	• 2
Number Of Conductors	14-2 AWG
Conductor Type	1
Conductor - Copper Str Size Range	<ul style="list-style-type: none"> • CU C Str-Size • AL C Str-Size

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	1
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	0.51 in
Package Height	3.450 in
Dimension - Height mm	14.2 mm
Dimension - Height inch	0.56 in
Dimension - Height fraction	14/25 in
Package Weight	0.920 lb.
Package Length	3.800 in
Package Width	3.500 in
Dimension - L Length Overall mm	29 mm
Dimension - Width fraction	1/2 in
Dimension - Hole Size mm	7 mm
Dimension - Hole Size inch	0.27 in
Dimension - Stud Size inch	1/4
Dimension - Bolt Hole Size inch	0.25 in
Dimension - Bolt Size fraction	1/4
Dimension - Width mm	13 mm
Dimension - Width inch	0.50 in
Dimension - D inch	0.63 in
Dimension - N inch	0.31 in
Dimension - Length Overall inch	1.16 in

Force Related

Installation Torque Recommended in-lb	50 LBS/in
---------------------------------------	-----------

General

Material - Hardware	Steel
---------------------	-------

Physical Attribute - Screw Type	Slot
Plated	Y
Sub Brand	UNIVERSAL TERM
UPC	781810370056
Type	Bolted Lugs & Terminals
Material	Aluminum
Plating Type	Tin
UPC 14 Digit GTIN	00781810370056

Minimum Pack Quantity	50
Pallet Quantity	51200
Carton Quantity	1800

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)

Logistics



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved
BRDY-KA2U-SPEC-EN | REV 5/2026