




P.	LYR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




DETAIL A-A




DETAIL P1




DETAIL P2




DETAIL P3




DETAIL D




DETAIL E




DETAIL N




DETAIL P




DETAIL S




DETAIL F




DETAIL R




DETAIL T




DETAIL G




DETAIL V




DETAIL M




DETAIL H




DETAIL W




DETAIL J




DETAIL X



DETAIL Y




DETAIL K




DETAIL Z

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. WELDON 18OCT2000	TE Connectivity	
		CHK D. BIEVENOUR 18OCT2000		
DIMENSIONS:		APVD D. BIEVENOUR 18OCT2000	NAME	
mm		PRODUCT SPEC		
		APPLICATION SPEC	SIZE	
		WEIGHT		
MATERIAL		CUSTOMER DRAWING	A100779	
SEE NOTES		C=796634		RESTRICTED TO
		SCALE 4:1		SHEET 2 OF 3
				REV R13



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



DETAIL AB



DETAIL AC

PRELIMINARY		NICKEL	TIN	7 9		DETAIL AC	25.40	5	8-796634-5	
		CLAMP PLATING	CONTACT PLATING	MARKING		SPECIAL	L	NO OF POSN	PART NUMBER	
				THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.WELDON 18OCT2000		 TE Connectivity		
						CHK D.BIEVENOUR 18OCT2000				
				DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME TERMINAL BLOCK, PLUG, STACKING, 5.08mm PITCH		
				mm		APVD D.BIEVENOUR 18OCT2000				
						PRODUCT SPEC		SIZE A1		
						APPLICATION SPEC				
						WEIGHT		CAGE CODE 00779		
						FINISH				
				SEE NOTES		CUSTOMER DRAWING		DRAWING NO C=796634		
						SCALE				
						SHEET		REV		
						OF				
						3		13		
						3				