

**Part Number :** [1200660279](#)

**Product Description :** Micro-Change (M12) Double-Ended Cordset, 4 Poles, A-Coded, Male (Straight) to Female (Straight), 22 AWG, Yellow PVC Cable, 4.0m (13.12') Length

**Series Number :** 120066

**Status :** Active

**Product Category :** Circular Industrial Cordsets

**Engineering Part Number :** 884030A09M040



---

## Documents and Resources


### Drawings

[1200660279\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

## Part Details

### General

Status	Active
Category	Circular Industrial Cordsets
Series	120066
Description	Micro-Change (M12) Double-Ended Cordset, 4 Poles, A-Coded, Male (Straight) to Female (Straight), 22 AWG, Yellow PVC Cable, 4.0m (13.12') Length
IP Rating	IP67
Product Name	Micro-Change (M12)
Type	Double Ended
UPC	78172553048

### Agency

CSA	LR6837
UL	E152210

### Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

### Physical

Cable Diameter	5.33mm (.210")
Cable Length	4.0m (13.12')
Color - Cable Jacket	Yellow

Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
Coupling Style	Threaded
Gender	Female-Male
Keyway	A-Coded
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	PUR
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	541.000/g
Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	UL 2661
Wire Size (AWG)	22

---

This document was generated on Dec 30, 2025