



183H16

Low Voltage P.C. Board Mounted Power Transformer



NOTE: Pin numbers are not on the unit. Instead, look for the paint dot. It is always on the secondary side. (pins 12-7).



Key Features:

- Universal operation on 50/60Hz, 115 or 230V dual primary for worldwide use.
- Low Profile, split bobbin with top shroud design
- Dual winding secondary, non-concentrically wound.
- Low Primary to secondary coupling with no electro-static shield required.
- High Insulation - Hipot of 4,000V RMS
- Class F Insulation - 155 degrees C.
- P.C. Board mount with industry standard pin spacing.
- Agency listings: cURus, CE, and TUV.

Mechanical - inches (mm)	
L	2.25 (57.2)
W	1.88 (47.8)
H	1.63 (41.4)
A	0.4 (10.2)
B	0.4 (10.2)
C	1.46 (37.1)
M	1.5 (38.1)
N	- (-)
P	- (-)
Pin Size	0.036 (0.9)
Screw Type	#4
Weight	0.9 lbs. / 0.41 kg
Electrical	
Size (VA)	20
Primary	115 / 230 VAC
Sec (Series)	16V C.T. @ 1.25A
Sec (Parallel)	8V @ 2.5A

Connection Information 183 Series Power Transformers

Primary Connections - 183 Series Transformers



Secondary Connections - 183 Series Transformers

