© 2016 TE Connectivity Ltd. family of companies. All Rights Reserved

HARNESSING

CABLE BRAIDS



✔ Active

TE CONNECTIVITY (TE)

LWB-103-6.0(100)

LWB-103-6.0(100)
TE Internal Number: EG3246-000

EU RoHS Compliant
EU ELV Compliant

Product Type Braid

Plating Nickel

Braid Material Copper Alloy

Braid Coverage (%) 90 (Min)

PRODUCT DRAWING
English

DOCUMENTATION

Product Drawings

INSTALITE LIGHTWEIGHT SCREENING BRAID
PDF
English

FEATURES

Please review product documents or contact us for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Product Type Braid

Electrical Characteristics

Downloaded from Arrow.com.

DC Resistance (Nominal) (mΩ) 18

Body Features

Plating Nickel
Braid Material Copper Alloy

Dimensions

Cable Entry Diameter 4.5 – 8 mm [.177 – .315 in]
Length (ft) 328.08
Length (m) 100
Weight (Nominal) (kg/km) 15.5

Usage Conditions

Operating Temperature Range (°C) -65 – 200

Packaging Features

Packaging Quantity 100
Packaging Method Reel

Other

Braid Coverage (%) 90 (Min)

Statement of Compliance

Statement of Compliance
PDF

Downloaded from Arrow.com.