Johanson Product Information for QCCP501Q470J1GV001T

Johanson Company: Johanson Technology inc.

Deprecated P/N: 501R14C470JV4T

Datasheet Date: 05-05-2022

Description: Capacitors Hi-Q, 0603, Hi-Q NP0/C0G, 500V, 47pF±5%, Ni/Sn (RoHS), 7" Reel Paper Tape

Life Cycle Stage: Active - Production

AEC Q200 Qualified: No

Schedule B: 8532.24.0020

Harmonization Code: 8532.24.00.20

ITAR: No

ECCN: EAR99

RoHS Compliance: Yes, RoHS 10/10

REACH: Yes

Country of Origin: US

Product Family: Capacitors

Product Subfamily: Capacitors High-Q MLC C-Series

Capacitance Value: 47.000

Cap Unit of Meas: pF

Tolerance: ±5%

Voltage: 500

Dielectric Temp Coefficient: Hi-Q NP0/C0G

Termination: Ni/Sn (RoHS)

Marking: No Mark

Product Release Date: 16 October, 2020

Web Page Link: https://www.johansontechnology.com/high-q-multi-layer-capacitors

Size for Capacitors (EIA): 0603

Specification Number: 35S0157

NCNR: No

Thickness (Max): 0.035

Thickness (Min): 0.027

End Band (Min): 0.008

End Band (Max): 0.020

Standard Item: No

Lead Time Typical (Weeks)*:
*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes. 8

Length (Min): 0.056

Length (Max): 0.068

Width (Min): 0.026

Width (Max): 0.038

Downloaded from Arrow.com.