




2310541-2 ✔ ACTIVE

TE Internal #: 2310541-2

Housing for Male Terminals, Sealable, Orange, Panel Mount, Key B

View on TE.com >

Connectors > Automotive Connectors > Automotive Housings

Connector & Housing Type: **Housing for Male Terminals**

Sealable: **Yes**

Primary Product Color: **Orange**

Connector Mounting Type: **Panel Mount**

Connector Position Assurance Capable: **No**

Features

Product Type Features

Connector & Housing Type	Housing for Male Terminals
Sealable	Yes
Primary Locking Feature	Integrated in Housing

Body Features

Primary Product Color	Orange
Connector & Keying Code	B

Mechanical Attachment

Connector Mounting Type	Panel Mount

Other

Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant

Downloaded from Arrow.com.

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Octamethylcyclotetrasiloxane (D4) (.5% in Component Part) Dodecamethylcyclohexasiloxane (D6) (.5% in Component Part) Decamethylcyclopentasiloxane (D5) (.5% in Component Part) **Article Safe Usage Statements:** Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts

TE Part # 2403935-1
FACIAL SEAL,HVA 280,GRN,HEADER

Customers Also Bought

Downloaded from Arrow.com.




TE Part #1452426-1
EXTRACTION TOOL



TE Part #680326-000
D-609-06



TE Part #2103245-6
Inner Housing, Split Hdr, Key F, HVA280



TE Part #680105-000
D-609-04



TE Part #1719043-1
SINGLE WIRE SEAL,GREEN



TE Part #680104-000
D-609-03



TE Part #680328-000
D-609-08



TE Part #1-968050-1
SPECIAL TERMINAL 11-10 AWG PTPB



TE Part #2103245-2
Inner Housing, Split Hdr, Key B, HVA280



TE Part #1-2103346-2
HVA280 2 Bay Header Sub-Assy, KEY D, F

Documents

Product Drawings

SPLIT HEADER ASSY, KEY B, HVA280, V0

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2310541-2_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2310541-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2310541-2_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Downloaded from Arrow.com.