




## Material Datasheet

20.03.2023

**TAG107TD3-1209-WHCL**  
Article Number 596-01209



Material:	Type 1209, Vinyl (1209)
Colour:	White (WH), Transparent (CL)
Operating Temperature :	-20 °C to +80 °C
Curing Temperature:	from 0 °C
Bundle Ø min.:	12.0 mm
Bundle Diameter max (metric):	37.5 mm
Self adhesive (Yes/No):	Yes
Width (W):	25.40 mm
Height (H):	31.75 mm
Height (H2):	149.86 mm
Width of Liner (WL):	82.0 mm
Labels per Row:	3 pcs.
Thickness of Foil:	90 µm
Adhesive:	Acrylic

We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved



## Material Datasheet

20.03.2023

Print Method: Thermal transfer print  
 Print Method (Alternative): Laser beam print  
 Application Tool: TT431, TT4030  
 Recommended Ribbon Type: TT932DOUT

Application Method: The functionality and durability of the labels can be negatively affected if improperly processed or applied. All surfaces to be bonded must be clean, dry as well as free from dust and grease. Avoid touching the adhesive surface of the label as this could impair the application performance.



We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved