





NOTE:

1. MATERIAL:
HOUSING: NYLON 6T (E630NK), UL94V-0
TERMINAL: C2700 H
2. FINISH:
TERMINAL: GOLD AT CONTACT,
G/F OVER 1um(40u") MIN Ni OVER ALL
3. SPEC.:
PRODUCT SPEC: GS-12-629
PACKING SPEC: GS-14-1517
4. THE HSG. WILL WITHSTAND EXPOSURE TO 260C
PEAK TEMP. FOR 10 SEC. IN A CONVECTION, INFRA-RED
OR VAPOR PHASE REFLOW OVEN.
5. MATING SIDE LENGTH: 2.50MM MIN.
6. PRODUCT NUMBERING:
200218 3 2 - XXX XX X X LF

LEAD FREE
PLATING:
1: G/F ALL OVER
4: 0.25um(10U") GOLD AT CONTACT
8: 0.76um(30U") GOLD AT CONTACT
PACKING
T: TUBE
D: TUBE + CAP
C: REEL + CAP (16 PIN)
PIN COUNT
04, 06, 08, ..., 48, 50
(EVERY EVEN PIN)
STACK HEIGHT "K"
EXAMPLE: 045=4.5MM
IN 0.5MM INCREMENT



Recommended P.C.B. Layout
Layout Tolerance = ± 0.05 mm

mat'l. code				surface		tolerance		projection		product family			
				ISO1302 ✓		ISO1101 ISO406				MINITEK			
ltr ecn ndr date				tolerances unless otherwise specified						title			
A	T10-0088	S.LIN	07/15/10	angle line slot	0.X±0.38				1.27X1.27MM BTB STACK HD VT, SMT				
B	BX-W-011534	ZK	05/04/12		0.XX±0.25								
					0'±2' 0.XXX±0.15								
							scale 5:1						
				dr	STERLING LIN	07/15/10			dwg no		sheet 1 of 1		size
				engr	STERLING LIN	07/15/10			20021832		A4		
				chr	STERLING LIN	07/15/10							
				appd	GARY HSIEH	07/15/10							
sheet	revision		B						type		Product Customer Drawing		
index	sheet		1										