


MODEL NO.	PACKAGING
145-0701-212	ONE PCS PER BAG


REV	ECO	DATE
001	ECO-19-0022	06/26/2019








RECOMMENDED MOUNTING PATTERN



DETAIL A (10/1)



NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIAL & FINISH:
   1.1 BODY: PASSIVATED STAINLESS STEEL
   1.2 CONTACT PIN: GOLD PLATED BERYLLIUM COPPER
   1.3 INSULATOR: PTFE, WHITE
   1.4 WASHER: STAINLESS STEEL
   1.5 BOLT: SUS302

2. ELECTRICAL:
   2.1 IMPEDANCE: 50 OHMS
   2.2 FREQUENCY RANGE: DC-40 GHz
   2.3 VOLTAGE STANDING WAVE RATIO: 1.35 MAX
   2.4 DIELECTRIC WITHSTANDING VOLTAGE: 750 VRMS MIN
   2.5 CONTACT RESISTANCE:
      2.5.1 CENTER CONTACT: 3 MILLIOHMS MAX
      2.5.2 OUTER CONTACT: 2 MILLIOHMS MAX
   2.6 INSULATOR RESISTANCE: 5000 MEGOHM MIN

3. MECHANICAL:
   3.1 ENGAGEMENT AND DISENGAGEMENT FORCE: 0.23 MN MAX
   3.2 CONTACT RETENTION: 22 N MIN
   3.3 DURABILITY: 500CYCLES MIN

4. ENVIRONMENT:
   4.1 OPERATING TEMPERATURE: -55 TO 125°C
   4.2 THERMAL SHOCK: MIL-STD-202, METHOD 107, CONDITION B.
   4.3 SHOCK: MIL-STD-202, METHOD 213, CONDITION I
   4.4 VIBRATION: MIL-STD-202, METHOD 204, CONDITION D
   4.5 MOISTURE RESISTANCE: MIL-STD-202, METHOD 106
   4.6 SALT SPRAY: MIL-STD-202, METHOD 101, CONDITION B

1. BOARD THICKNESS: 1.57-2.79mm

THIS PROPRIETARY Document is property of Cinch Connectivity Solutions and contains trade secrets, copyrighted, and confidential information. By accepting and understanding that it is not to be reproduced in whole or in part without prior written permission of Cinch Connectivity Solutions. INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2009.

Model No.	145-0701-211/220		Johnson
RoHS2 2011/65/EU	Cage Code		Title: JACK, PCB, COMPRESSION MOUNT,SIDE GROOVE,2.92mm (SMK)
UNLESS OTHERWISE SPECIFIED: .XXX ±.02 .XXXX ±.01 ANGLES ±5°	3RD ANGLE PROJECTION		Drawing No. 145-0701-211/220 Rev. 001
	Drawn By: Betty.Yu		
	Date: 06/26/2019	Size C / DO NOT SCALE DRAWING	Workmanship Std: NONE / Sheet 1 of 1

Please read our datasheet & drawing disclaimer here.

Downloaded from Arrow.com.