








NOTES:

1. MATERIALS:

HOUSING - THERMOPLASTIC, BLUE
SHELL - STEEL, NICKEL PLATED
TERMINALS - COPPER ALLOY, GOLD PLATED ON CONTACT AREA
TIN PLATED ON SOLDER TAIL

2. ELECTRICAL CHARACTERISTICS:

CONTACT RESISTANCE - 30m OHMS MAX
INSULATION RESISTANCE - 1000M OHMS MIN @ 500V DC
CURRENT RATING - 1.5A MAX
DIELECTRIC WITHSTANDING - 500V AC FOR 1 MINUTE

3. OPERATION TEMPERATURE - -30°C TO +85°C

4. THIS PRODUCT IS RoHS COMPLIANT.

CUSTOMER DRAWING

					UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES [mm] - TWO PLACE DECIMALS ±0.02 [0.5] - THREE PLACE DECIMALS ±0.008 [0.20]	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.											
						SIZE	WIDTH		MULT		LBS/M		TEMPER				
						FINISH SPEC No.						MATERIAL SPEC No.					
						FIRST USED ON				SCALE 4:1		Switchcraft®					
						DATE DRAWN 8/30/22		BY MK	CHKD MK 10/19/22		APVD MK 10/19/22						
A	28548	10/26/22	PC	TJK								SHEET 1 OF 1					
REV	ECO NUMBER	DATE	BY	APVD								PART No. PCUA30E				REV A	
REVISIONS					DO NOT SCALE DRAWING												