

## SILVYN® MSK-M US

SILVYN® MSK-U-M - nickel-plated brass conduit fitting with integrated cable strain relief

### Info

Integrated SKINTOP® cable strain relief



Wide clamping range



Maximum vibration protection



Mechanical resistance



Assembly time



Robust



Reliability



Integrated SKINTOP® cable gland

### Benefits

Optimum cable and conduit strain relief

Maximum cable sealing

Fast and easy assembly

Wide clamping range

Anti-turn protection

### Application range

Last Update (01.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## SILVYN® MSK-M US

In combination with protective conduit:

SILVYN® AS/AS-P/EDU-AS/EMC AS-CU

Indoor / outdoor applications

Used in areas where cables and wires need to be provided with strain relief and additional sealing

### Product features

Combination of SILVYN® and SKINTOP®

### Product Make-up

Optional:

SKINTOP® MS-M cable gland or

SKINTOP® MS-SC-M EMC connection

SILVYN® conduit connection via inner sleeve and cap nut

### Note

For suitable accessories, refer to SKINTOP® metric accessories

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001180

ETIM 5.0 Class-Description: Screw connection for protective metallic hose

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001180

ETIM 6.0 Class-Description: Screw connection for protective metallic hose

Material:

Basis type:

Body: nickel-plated brass

Conduit connector seal: CR/NBR

Tube seal: TPE

Protection rating:

Cable: IP 68

Conduit:

IP 40 with SILVYN® AS, EDU-AS, EMC AS-CU

IP 65 with SILVYN® AS-P

Temperature range:

-30°C to +100°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

# SILVYN® MSK-M US

| Article number                                         | Metric size | Clamping range in mm | Clear opening (mm) | Suitable for conduit Ø (mm) | Pieces / PU |
|--------------------------------------------------------|-------------|----------------------|--------------------|-----------------------------|-------------|
| SILVYN® MSK-M for SILVYN® AS                           |             |                      |                    |                             |             |
| 55506080                                               | 12 x 1.5    | 3.0 - 7.0            | 6.3                | 10                          | 5           |
| 55506081                                               | 16 x 1.5    | 4.5 - 10.0           | 9                  | 14                          | 5           |
| 55506082                                               | 20 x 1.5    | 7.0 - 13.0           | 11.5               | 17                          | 5           |
| 55506083                                               | 25 x 1.5    | 9.0 - 17.0           | 14.5               | 21                          | 5           |
| 55506084                                               | 32 x 1.5    | 11.0 - 21.0          | 19.5               | 27                          | 5           |
| 55506085                                               | 40 x 1.5    | 19.0 - 28.0          | 26.5               | 36                          | 1           |
| 55506086                                               | 50 x 1.5    | 27.0 - 35.0          | 36                 | 45                          | 1           |
| 55506087                                               | 63 x 1.5    | 34.0 - 45.0          | 45.5               | 56                          | 1           |
| SILVYN® MSK-M for SILVYN® AS-P / EDU-AS / EMC AS-CU    |             |                      |                    |                             |             |
| 55506090                                               | 12 x 1.5    | 3.0 - 7.0            | 6.3                | 10                          | 5           |
| 55506091                                               | 16 x 1.5    | 4.5 - 10.0           | 9                  | 14                          | 5           |
| 55506092                                               | 20 x 1.5    | 7.0 - 13.0           | 11.5               | 17                          | 5           |
| 55506093                                               | 25 x 1.5    | 9.0 - 17.0           | 14.5               | 21                          | 5           |
| 55506094                                               | 32 x 1.5    | 11.0 - 21.0          | 19.5               | 27                          | 5           |
| 55506095                                               | 40 x 1.5    | 19.0 - 28.0          | 26.5               | 36                          | 1           |
| 55506096                                               | 50 x 1.5    | 27.0 - 35.0          | 36                 | 45                          | 1           |
| 55506097                                               | 63 x 1.5    | 34.0 - 45.0          | 45.5               | 56                          | 1           |
| SILVYN® MSK-SC-M for SILVYN® AS                        |             |                      |                    |                             |             |
| 55506110                                               | 12 x 1.5    | 3.0 - 7.0            | 6.3                | 10                          | 5           |
| 55506111                                               | 16 x 1.5    | 4.5 - 10.0           | 9                  | 14                          | 5           |
| 55506112                                               | 20 x 1.5    | 7.0 - 13.0           | 11.5               | 17                          | 5           |
| 55506113                                               | 25 x 1.5    | 9.0 - 17.0           | 14.5               | 21                          | 5           |
| 55506114                                               | 32 x 1.5    | 11.0 - 21.0          | 19.5               | 27                          | 5           |
| 55506115                                               | 40 x 1.5    | 19.0 - 28.0          | 26.5               | 36                          | 1           |
| 55506116                                               | 50 x 1.5    | 27.0 - 35.0          | 36                 | 45                          | 1           |
| SILVYN® MSK-SC-M for SILVYN® AS-P / EDU-AS / EMC AS-CU |             |                      |                    |                             |             |
| 55506120                                               | 12 x 1.5    | 3.0 - 7.0            | 6.3                | 10                          | 5           |
| 55506121                                               | 16 x 1.5    | 4.5 - 10.0           | 9                  | 14                          | 5           |
| 55506122                                               | 20 x 1.5    | 7.0 - 13.0           | 11.5               | 17                          | 5           |
| 55506123                                               | 25 x 1.5    | 9.0 - 17.0           | 14.5               | 21                          | 5           |
| 55506124                                               | 32 x 1.5    | 11.0 - 21.0          | 19.5               | 27                          | 5           |
| 55506125                                               | 40 x 1.5    | 19.0 - 28.0          | 26.5               | 36                          | 1           |
| 55506126                                               | 50 x 1.5    | 27.0 - 35.0          | 36                 | 45                          | 1           |

Last Update (01.09.2020)


©2020 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## SILVYN® MSK-M US



Last Update (01.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16