





Lever height of 5.5mm, mountable directly on panels.




- Rating (max.)/(min.) (Resistive load): 0.2A 30V DC/50μA 3V DC
- Contact resistance (Initial performance/After lifetime):
20mΩ max./40mΩ max.
- Operating life without load: 10,000 cycles 40mΩ max.
- Operating life with load (at max. rated load): 10,000 cycles 40mΩ max.



2.5mm-travel Horizontal Type
SPPJ2 Series**Drawing No.2**

■ Dimensions



■ Circuit Diagram

