



Part Number : [190270088](#)
Product Description : ATP Crimp Dies for the
Tape Crimp Module and ATP-101 & 301 Press
Series Number : 207126
Status : Active
Product Category : Applicators and Crimp
Modules
Engineering Number : ATP-C-130



Documents & Resources

Tooling Specifications

- [ATS-190270088-001.pdf](#)
- [ATS-TOOLING-ID-ATP-001.pdf](#)
- [TM-640160065-001.pdf](#)
- [TM-640160065CN-001.pdf](#)
- [TM-640160065DE-001.pdf](#)
- [TM-640160065SP-001.pdf](#)
- [TM-640160065FR-001.pdf](#)
- [TM-640160065IT-001.pdf](#)
- [TM-640160065JP-001.pdf](#)
- [TM-640160065KR-001.pdf](#)
- [TM-640160065MY-001.pdf](#)
- [TM-640160065PL-001.pdf](#)
- [TM-640160065RU-001.pdf](#)
- [TM-640160065SK-001.pdf](#)
- [TM-640160065TH-001.pdf](#)
- [TM-640160065VN-001.pdf](#)
- [TM-640160065TW-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant

REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Applicators and Crimp Modules
Series	207126
Description	ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press
Comments	The Crimp Tape Module 640162000 is a base unit that will work like an applicator in a Molex TM-3000 638017200, 638017300 industry standard crimp press or the Molex TM-4000 638017600 industry standard crimp press. The Crimp Tape Module will accept all ATP-301 and ATP-201 style crimp dies. This Crimp Tape Module will allow customers to process most of Molex's Mylar Tape product from 2 AWG uninsulated and 4 AWG insulated products and up. The Crimp Tape Module will NOT work in any other industry standard crimp press or wire process machine. These ATP-301 style die sets can be used in the older style suitcase presses.
Function	Crimp
Geographic Area	Global
Level of Automation	Semi-Automatic

More Detailed Tech Information	toolingsupport@molex.com
Product Name	N/A
Tool Type	Crimp Module
UPC	800753041103
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight	1.000/g
------------	---------

Use with Part(s)

Description	Part Number
Taped Terminal Crimp Module used with TM-3000 and TM-4000 presses with ATP-201 and ATP-301 die sets.	<u>640162000</u>
Use With	Molex ATP-101 style presses

Applicable Parts

Description	Part Number
Krimptite Ring Tongue Terminal for 16-14 AWG, Stud Size 10, 19.94mm Length, Mylar Tape Carrier	<u>190440164</u>
Krimptite Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 4 (M2.6), Length 19.94mm, Mylar Tape Carrier	<u>190690147</u>

Krimptite Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 8 (M4), Length 19.94mm, Mylar Tape Carrier	<u>190690208</u>
Krimptite Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 10 (M5), Length 19.94mm, Mylar Tape Carrier	<u>190690212</u>
Krimptite Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 10 (M5), Length 24.18mm, Mylar Tape Carrier	<u>190690218</u>
Krimptite Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 1/4" (M6), Length 24.18mm, Mylar Tape Carrier	<u>190690221</u>
Krimptite Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 5/16" (M8), Length 24.18mm, Mylar Tape Carrier	<u>190690225</u>
Krimptite Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 6 (M3.5), Length 18.82mm, Mylar Tape Carrier	<u>190690232</u>
Krimptite Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 8 (M4), Length 18.82mm, Mylar Tape Carrier	<u>190690235</u>
Krimptite Snap Spade Terminal, for 12-10 AWG Wire, Stud Size 5 (M3), 16.87mm Length	<u>190980070</u>
Krimptite Snap Spade Terminal, for 12-10 AWG Wire, Stud Size 10 (M5), 19.60mm Length	<u>190980091</u>
Krimptite Flanged Spade Tongue Terminal for 12-10 AWG Wire, Stud Size 8 (M4), Length 19.91mm, Mylar Tape Carrier	<u>191180081</u>
Krimptite Flanged Spade Tongue Terminal for 12-10 AWG Wire, Stud Size 10 (M5), Length 19.91mm, Mylar Tape Carrier	<u>191180083</u>
Krimptite Flanged Spade Tongue Terminal for 12-10 AWG Wire, Stud Size 8 (M4), Length 19.56mm, Mylar Tape Carrier	<u>191180087</u>
Krimptite Flanged Spade Tongue Terminal for 12-10 AWG Wire, Stud Size 10 (M5), Length 19.56mm, Mylar Tape Carrier	<u>191180090</u>
Krimptite Spade Tongue Terminal for 12-10 AWG Wire, Tape and Reel	<u>191410086</u>

Krimptite Butt Splice for 12-10 AWG Wire	<u>191890017</u>
VersaKrimp Ring Tongue Terminal for 12-10 AWG Wire, Closed-Brazed Barrel, Stud Size 5-6 (M3-3.5), Mylar Tape Carrier	<u>191930105</u>
VersaKrimp Ring Tongue Terminal for 12-10 AWG Wire, Closed-Brazed Barrel, Stud Size 10 (M5), Mylar Tape Carrier	<u>191930111</u>
VersaKrimp Ring Tongue Terminal for 12-10 AWG Wire, Closed-Brazed Barrel, Stud Size 10 (M5), Mylar Tape Carrier	<u>191930113</u>
VersaKrimp Ring Tongue Terminal for 12-10 AWG Wire, Closed-Brazed Barrel, Stud Size 8 (M4), Mylar Tape Carrier	<u>191930131</u>
Krimptite Temp-Term Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 6 (M3.5), Mylar Tape Carrier	<u>192030092</u>
Krimptite Temp-Term Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 10 (M5), Mylar Tape Carrier	<u>192030094</u>
Krimptite Temp-Term Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 1/4" (M6), Mylar Tape Carrier	<u>192030095</u>
VersaKrimp Temp-Term Ring Tongue Terminal for 12-10 AWG, Stud Size 8 (M4), Mylar Tape Carrier	<u>192030098</u>
VersaKrimp Temp-Term Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 10 (M5), Mylar Tape Carrier	<u>192030100</u>
VersaKrimp Temp-Term Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 1/4" (M6), Mylar Tape Carrier	<u>192030101</u>
Krimptite Temp-Term Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 10 (M5), Mylar Tape Carrier	<u>192030114</u>
Krimptite Wire Pin Terminal for 12-10 AWG Wire, Mylar Tape Carrier	<u>192110002</u>
Step Down Butt Splice for 16-10 AWG Wire, Tape and Reel	<u>192150027</u>
VersaKrimp Butt Splice for 12-10 AWG Wire, Tape and Reel	<u>192150030</u>
VersaKrimp Metric Ring Terminal for M4 Stud Size (#8), Un-insulated, Adhesive Tape on Reel	<u>193230218</u>

VersaKrimp Metric Ring Terminal for M3 Stud Size (#5), Un-insulated, Adhesive Tape on Reel	<u>193230220</u>
VersaKrimp Metric Ring Terminal for M6 Stud Size (1/4"), Un- insulated, Adhesive Tape on Reel	<u>193230221</u>
VersaKrimp Metric Ring Terminal for M8 Stud Size (5/16"), Un- insulated, Adhesive Tape on Reel	<u>193230222</u>
VersaKrimp Metric Ring Terminal for M10 Stud Size (7/16"), Un- insulated, Adhesive Tape on Reel	<u>193230223</u>

This document was generated on Nov 09, 2024