


# 2057426-3 Product Details

 Share  Print  Email



 Active

## Impact High Density Backplane Connectors


IMP100,S,H,V2P10C,UG,46,5.5

2057426-3 


TE Internal Number: 2057426-3

### Product Highlights [View All](#)

- Connector Style = Header
- 40/Signal, 20/Ground
- 60 Positions
- Header Type = Partially Shrouded
- Board-to-Board Configuration = Right Angle, Vertical

Pricing & Availability 

Request Sample 

Add to My Part List 

Buy Product through Distributor 

 Feedback


Documents

Features

Compliance

**Please Note:**  
Use the Product Drawing for all design activity

| Product Type Features    |                       |
|--------------------------|-----------------------|
| PCB Mount Retention Type | Action/Compliant Tail |
| PCB Mount Alignment Type | None                  |




| Electrical Characteristics  |   |
|-----------------------------|---|
| Impedance (Ω)               | 100   |
| Operating Voltage Reference | AC/DC   |
| Operating Voltage (VAC)     | 120  |
| Operating Voltage (VDC)     | 120   |


| Dimensions                        |                |
|-----------------------------------|----------------|
| Tail Length (mm [in])             | 1.2 [0.047]    |
| Length (X-Axis) (mm [in])         | 18.90 [0.7441] |
| Width (Z-Axis) (mm [in])          | 12.70 [0.500]  |
| Profile Height (Y-Axis) (mm [in]) | 11.95 [0.470]  |
| PCB Hole Diameter (mm [in])       | 0.46 [0.018]   |

| Body Features |                    |
|---------------|--------------------|
| Header Type   | Partially Shrouded |

| Contact Features  |                       |
|---|-----------------------|
| Contact Type  | Pin                   |
| Contact Length (mm [in])                                | 5.50 [0.217]          |
| Contact Plating, Termination Area, Material             | Matte Tin             |
| Contact Plating, Termination Area, Thickness (µm [µin]) | 1.27 [50]             |
| Contact Base Material                                   | Copper-Nickel-Silicon |
| Underplate Material                                     | Nickel                |
| Underplate Material Thickness (µm [µin])                | 1.27 [50.000]         |

| Housing Features  |                              |
|-------------------|------------------------------|
| Connector Style   | Header                       |
| End Wall Location | Open                         |
| Housing Color     | Black                        |
| Housing Material  | LCP (Liquid Crystal Polymer) |

| Configuration Features  |  |  |
|---|--|--|
| Connector Contact Configuration (No. of Pos./Type)  | 40/Signal, 20/Ground   |  |
| Number of Positions  | 60   |  |
| Number of Differential Pairs Per Column   | 2  |  |
| Number of Columns   | 10   |  |
| Number of Rows       | 6  |  |
| Shrouded  | Yes - Partial  |  |
| Guide Location  | Unguided  |  |
| Tail Orientation  | In-line  |  |

| Industry Standards   |                                    |
|--|------------------------------------|
| RoHS/ELV Compliance         | RoHS compliant, ELV compliant      |
| Lead Free Solder Processes  | Not relevant for lead free process |
| RoHS/ELV Compliance History  | Always was RoHS compliant          |
| UL Rating  | Recognized                         |
| UL File Number   | E28476                             |
| UL Flammability Rating   | UL 94V-0                           |
| CSA Certified  | Yes                                |

| Environmental                   |                        |
|---------------------------------|------------------------|
| Operating Temperature (°C [°F]) | -55 - +85 [-67 - +185] |

| Conditions for Usage         |                       |
|------------------------------|-----------------------|
| Board-to-Board Configuration | Right Angle, Vertical |

| Operation/Application |                             |
|-----------------------|-----------------------------|
| Industry Application  | Networking (Communications) |

| Packaging Features |          |
|--------------------|----------|
| Packaging Method   | Tube/Box |

| Other |                 |
|-------|-----------------|
| Brand | TE Connectivity |

### Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

