


T4081NSN7TTB (Active)

QorIQ, 64b Power, 8x 1.8GHz threads, 1.87G DDR3L, 4x10GE, crypto disabled, 0-105C, Rev 2, lo pwr

- Data Sheet
- Product Summary
- Software & Tools
- Documentation



Package :
BGA1932
BGA1932, plastic, ball grid array; 1932 balls; 1 mm pitch; 45 mm x 45 mm x 3.18 mm body

Buy Options | Operating Characteristics | Environmental Information | Quality Information | Shipping Information

Buy Options

T4081NSN7TTBActiveTRAY-Tray, Bakeable, Multiple in Drypack

Distributor

935313235557

Min. Package Quantity: 12

Lead Time: 20 weeks

Operating Characteristics

Parameter	Value
Description	QorIQ, 64b Power, 8x 1.8GHz threads, 1.87G DDR3L, 4x10GE, crypto disabled, 0-105C, Rev 2, lo pwr

Environmental Information

Material Declaration	PbFree	EU RoHS	Halogen Free	RHF Indicator	2nd Level Interconnect	REACH SVHC	Weight (mg)
T4081NSN7TTB (935313235557)	Yes	Yes	Yes	D	e1	REACH SVHC	29211.9

Quality Information

Material Declaration	Safe Assure Functional Safety	Moisture Sensitivity Level (MSL)	Peak Package Body Temperature (PPT) (C°)	Maximum Time at Peak Temperatures (s)
		Lead Free Soldering	Lead Free Soldering	Lead Free Soldering
T4081NSN7TTB (935313235557)	No	3	250	30

Shipping Information

Part Number	Harmonized Tariff (US) Disclaimer	Export Control Classification Number (US)
T4081NSN7TTB (935313235557)	854231	3A991A1

ABOUT NXP

Investors
Press, News, Blogs

RESOURCES

Mobile Apps
Contact Us

FOLLOW US



News 11 Dec 2017

Safe and Reliable Industrial Control, Infotainment and Digital Clusters with i.MX 8X Ecosystem Partners

[Read More](#)

