




HEAT SHRINK TUBING



✓ Active

TE CONNECTIVITY (TE)
HTAT-12/3-0-STK
[Raychem](#) | [HTAT](#)

[HTAT-12/3-0-STK](#)
TE Internal Number: 7465232006
Alias ID: 7-1195823-7

[EU RoHS Compliant](#)
[EU ELV Compliant](#)

Wall Type Dual
Resistant To Fluids, Mechanical Damage, Strain
Low Outgassing No
Product Source Czech Republic
Packaging Method Stick

DOCUMENTATION

Catalog Pages/Data Sheets

HTAT Pages From 9-1773447-9

PDF
English

At-Application-Tooling-For-Raychem-Heat-Shrink-Product-2-1773452-8

PDF
English

Product Specifications

Product Specification

HTAT Sleeving

PDF
English

Product Environmental Compliance

Safety Data Sheet

Aliphatic Polyamide Based Adhesives.

PDF

English

Aliphatic Polyamide Based Adhesives.

PDF

Dutch

Aliphatic Polyamide Based Adhesives.

PDF

English

Aliphatic Polyamide Based Adhesives.

PDF

French

Aliphatic Polyamide Based Adhesives.

PDF

German

Aliphatic Polyamide Based Adhesives.

PDF

Italian

Aliphatic Polyamide Based Adhesives.

PDF

Spanish

Aliphatic Polyamide Based Adhesives.

PDF

Swedish

Instruction Sheets

Instruction Sheet (U.S.)

Global Dimensional Life For RAYCHEM Heat Shrink Tubing Standard Size Products (Customer Distribution)

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

Wall Type Dual

Product Family HTAT

Electrical Characteristics

Voltage (Max) (kV) .6

Body Features

Shrink Ratio 4:1
Color Black
Flexibility Semi-Flexible
Material Irradiated Modified Polyolefin
Fluid Type Diesel Fuel, Hydraulic Fluid, Lubricating Oil, Motor Oil, Water

Dimensions

Expanded Inside Diameter (Min) 12 mm [.472 in]
Recovered Wall Thickness (Nominal) 1.4 mm [.055 in]
Recovered Inside Diameter (Max) 3 mm [.118 in]
Recovered Wall Thickness (Tolerance) .3 mm [.012 in]
Cut Length 1220 mm [48.031 in]

Usage Conditions

Shrink Temperature (Min) (°C) 80
Resistant To Fluids, Mechanical Damage, Strain
Recovery Temperature (°C) 110
Operating Temperature Range (°C) -55 – 125
Flammability Flame-Retardant
Fluid Resistance Moisture/Spray Protection, Splash Protection

Product Availability

Applicable Region Global

Packaging Features

Packaging Method Stick

Other

Low Outgassing No
Product Source Czech Republic

PRODUCT COMPLIANCE

+

Statement of Compliance

Statement of Compliance
PDF