



Part Number : 350230016

Product Description : 2.00mm Pitch, Board-In Crimp Housing, Right-Angle and Vertical, 16 Circuits, Natural

Series Number : 35023


Status : New Business Not Supported

Product Category : Connector Housings

Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	New Business Not Supported
Category	Connector Housings

Series	35023
Description	2.00mm Pitch, Board-In Crimp Housing, Right-Angle and Vertical, 16 Circuits, Natural
Application	Signal, Wire-to-Board
Product Family	Board-in Connectors
Product Name	Board-in
UPC	800754879101

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	16
Color - Resin	Natural
Flammability	94V-0
Gender	N/A
Glow-Wire Capable	No
Material - Resin	Nylon
Net Weight	0.313/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

This document was generated on Jul 29, 2024