Part Number : 1200870041
Product Description : Nano-Change (M8) Double-Ended Cordset, 5 Poles, B-Coded, Male (Straight) to Female (Straight), 24 AWG, Yellow PVC Cable, 5.0m (16.40') Length
Series Number : 120087
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Part Number : 445030A10M050



Documents and Resources

Drawings

1200870041_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Relevant
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120087
Description	Nano-Change (M8) Double-Ended Cordset, 5 Poles, B-Coded, Male (Straight) to Female (Straight), 24 AWG, Yellow PVC Cable, 5.0m (16.40') Length
IP Rating	IP67
Product Name	Nano-Change (M8)
Protocol	N/A
Type	Double Ended
UPC	78678832997

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	30V AC / 36V DC

Physical

Cable Diameter	5.08mm (.200")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Yellow
Connector End A	Nano-Change (M8)

Downloaded from Arrow.com.

Connector End B	Nano-Change (M8)
Coupling Style	Threaded
Gender	Female-Male
Keyway	B-Coded
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	4.620/g
Orientation	Straight to Straight
Poles	5
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	UL 2661
Wire Size (AWG)	24

Downloaded from Arrow.com.