


**Part Number :** 2125280630
**Product Description :** Micro-Fit+ Versa Color Right-Angle Header, Through Hole, 3.00mm Pitch, Dual Row, 6 Circuits, 1.52µm Matte Tin (Sn) Plating, Glow-Wire Capable, Blue
**Series Number :** 212528
**Status :** Active
**Product Category :** PCB Headers and Receptacles

## Documents and Resources

### Drawings

2125280630_sd.pdf

2125280000-PK-000.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

### Specifications

2064600001-AS-000.pdf

2064600000-PS-000.pdf

2064600000-TS-000.pdf

2064600001-TS-000.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Compliant with Exemption 44; 33 |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Downloaded from Arrow.com.

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | PCB Headers and Receptacles |
| Series | 212528 |
| Description | Micro-Fit+ Versa Color Right-Angle Header, Through Hole, 3.00mm Pitch, Dual Row, 6 Circuits, 1.52µm Matte Tin (Sn) Plating, Glow-Wire Capable, Blue |
| Application | Wire-to-Board |
| Component Type | PCB Header |
| Product Name | Micro-Fit+ Versa Color |
| UPC | 196823365768 |

### Agency

| | |
|---|---|
| CSA | LR19980 |
| UL | E29179 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 10.6A |
| Voltage - Maximum | 600V AC (RMS)/DC |

Downloaded from Arrow.com.

### Physical

| | |
|---|---|
| Breakaway | No |
| Circuits (Loaded) | 6 |
| Circuits (maximum) | 6 |
| Color - Resin | Blue |
| Durability (mating cycles max) | 25 |
| First Mate / Last Break | No |
| Flammability | 94V-0 |
| Glow-Wire Capable | Yes |
| Keying to Mating Part | Yes |
| Lock to Mating Part | Yes |
| Material - Metal | Copper Alloy |
| Material - Plating Mating | Matte Tin |
| Material - Plating Termination | Tin |
| Material - Resin | Liquid Crystal Polymer (LCP) |
| Mounting Style | Through Hole |
| Net Weight | 0.950/g |
| Number of Rows | 2 |
| Orientation | Right Angle |
| Packaging Type | Tray |
| PCB Thickness - Recommended | 1.57mm |
| PC Tail Length | 3.18mm |
| Pitch - Mating Interface | 3.00mm |
| Pitch - Termination Interface | 3.00mm |
| Plating min - Mating | 1.520µm |
| Plating min - Termination | 1.520µm |
| Polarized to Mating Part | Yes |
| Polarized to PCB | Yes |
| Shrouded | Shrouded |
| Temperature Range - Operating | -40° to +125°C |
| Termination Interface Style | Through Hole |

---

## Mates With / Use With

### Mates with Part(s)

Downloaded from Arrow.com.

| Description | Part Number |
| --- | --- |
| Micro-Fit+ Dual Row Receptacle Housings | 206461 |



Downloaded from Arrow.com.