




REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED
B	REVISED PER ECN # T-5871	4-13-84	JB

NOTES:

- MATERIAL;** 1-A SOCKET WAFER; INSERT MATERIAL HIGH GRADE POLYARYLENE THERMOPLASTIC
1-B SOCKET CONTACT; COPPER ALLOY PER QQ-B-750
1-C SOLDERSLEEVE® TERMINATOR; REFER TO RAYCHEM DWG. CTA-0068 FOR DATA.
- FINISH;** 2-A SOCKET WAFER; FINISH TO BE MOLDED
2-B SOCKET CONTACT ENGAGING AREA; GOLD PLATE PER MIL-G-45204, CLASS I
2-C CONTACT TAIL; SOLDER COATED PER QQ-S-571 Sn63
- WAFER;** WAFER DESIGNED FOR USE WITH CONNECTORS DESIGNED TO *Raychem* SPECIFICATION D-6012
- SOCKET ONE;** SOCKET NUMBER ONE MARKED IN CONTRASTING COLOR.
- WEIGHT (MAX);**

LBS.	GRAMS
.0054	2.46

If this document is printed it becomes uncontrolled.
Check with the web for latest revision.

© Raychem Corporation 1983

SPECIFICATION CONTROL DRAWING

ITEM	QTY	PART NO.	DWG OR SPEC. NO.	DESCRIPTION
PARTS LIST				
THIRD ANGLE PROJECTION		MATERIAL	DRAWN Pence	DATE 4-11-83
		FINISH	CHECKED K	DATE 4-16-83
			APPROVED S	DATE 4-22-83
NEXT ASSY		USED ON		
THIS DRAWING AND THE INFORMATION SET FORTH HEREON ARE THE PROPERTY OF RAYCHEM CORPORATION AND ARE TO BE HELD IN TRUST AND CONFIDENCE. PUBLICATION, DUPLICATION, DISCLOSURE, OR USE FOR ANY PURPOSE NOT EXPRESSLY AUTHORIZED IN WRITING BY RAYCHEM CORPORATION IS PROHIBITED.		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES AND TOLERANCES ARE:		DEC .XX ±.02 DEC .XXX ±.005 ANGLES ± MM ±
		PROJECT NO.		
		FSCM NO. B 06090		DWG NO. MTC100-YBI-008
		SCALE NONE		DO NOT SCALE THIS DWG
		SHEET 1 OF 1		

Raychem

RAYCHEM CORPORATION
300 CONSTITUTION DRIVE
MENLO PARK, CALIFORNIA 94025

TITLE
WAFER "B1" SOCKET, SPECIAL 1" FOR USE IN
MTC100 2" CONNECTOR, 125°C OPERATING TEMP.
FOR 20-26 AWG ROUND WIRE TERMINATION,
OVAL ENTRY, MTC100 SERIES (P.A.S.S.)