

Complementary N & P-Channel Power MOSFET

FEATURES

- Low gate charge for fast power switching
- 100% UIS and R_g tested
- Compliant to RoHS directive 2011/65/EU and in accordance to WEEE 2002/96/EC
- Halogen-free according to IEC 61249-2-21

APPLICATIONS



- Building technologies
- DC Fan
- Motor drives

KEY PERFORMANCE PARAMETERS

PARAMETER		TYPE	VALUE	UNIT
V_{DS}		Q1	60	V
		Q2	-60	
$R_{DS(on)}$ (max)	$V_{GS} = 10V$	Q1	103	mΩ
	$V_{GS} = 4.5V$		122	
	$V_{GS} = -10V$	Q2	180	
	$V_{GS} = -4.5V$		220	
Q_g		Q1	4.4	nC
		Q2	4.6	



SOP-8



Note: MSL 1 (Moisture Sensitivity Level) per J-STD-020

ABSOLUTE MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

PARAMETER		SYMBOL	Q1	Q2	UNIT
Drain-Source Voltage		V_{DS}	60	-60	V
Gate-Source Voltage		V_{GS}	± 20	± 20	V
Continuous Drain Current	$T_C = 25^\circ\text{C}$	I_D	5	-4	A
	$T_A = 25^\circ\text{C}$		2.5	-2	
Pulsed Drain Current (Note 1)		I_{DM}	20	-16	A
Single Pulse Avalanche Current (Note 2)		I_{AS}	6.8	-7	A
Single Pulse Avalanche Energy (Note 2)		E_{AS}	6.9	7.4	mJ
Total Power Dissipation	$T_C = 25^\circ\text{C}$	P_D	5.7	5.7	W
	$T_C = 125^\circ\text{C}$		1.1	1.1	
Total Power Dissipation	$T_A = 25^\circ\text{C}$	P_D	1.4	1.4	W
	$T_A = 125^\circ\text{C}$		0.3	0.3	
Operating Junction and Storage Temperature Range		T_J, T_{STG}	- 55 to +150		$^\circ\text{C}$

THERMAL PERFORMANCE

PARAMETER	SYMBOL	MAXIMUM	UNIT
Thermal Resistance – Junction to Case	$R_{\theta JC}$	22	$^\circ\text{C/W}$
Thermal Resistance – Junction to Ambient	$R_{\theta JA}$	88	

Thermal Performance Note: $R_{\theta JA}$ is the sum of the junction-to-case and case-to-ambient thermal resistances. The case-thermal reference is defined at the solder mounting surface of the drain pins. $R_{\theta JC}$ is guaranteed by design while $R_{\theta CA}$ is determined by the user's board design. The $R_{\theta JA}$ limit presented here is based on mounting on a 1 in² pad of 2 oz copper.

ELECTRICAL SPECIFICATIONS (T _A = 25°C unless otherwise noted)							
PARAMETER	CONDITIONS	SYMBOL	TYPE	MIN	TYP	MAX	UNIT
Static							
Drain-Source Breakdown Voltage	V _{GS} = 0V, I _D = 250μA	BV _{DSS}	Q1	60	--	--	V
	V _{GS} = 0V, I _D = -250μA		Q2	-60	--	--	
Gate Threshold Voltage	V _{GS} = V _{DS} , I _D = 250μA	V _{GS(TH)}	Q1	1.2	1.8	2.5	V
	V _{GS} = V _{DS} , I _D = -250μA		Q2	-1	-1.5	-2.5	
Gate-Source Leakage Current	V _{GS} = ±20V, V _{DS} = 0V	I _{GSS}	Q1	--	--	±100	nA
	V _{GS} = ±20V, V _{DS} = 0V		Q2	--	--	±100	nA
Drain-Source Leakage Current	V _{GS} = 0V, V _{DS} = 60V	I _{DSS}	Q1	--	--	1	μA
	V _{GS} = 0V, V _{DS} = -60V		Q2	--	--	-1	
Drain-Source On-State Resistance ^(Note 3)	V _{GS} = 10V, I _D = 2.5A	R _{DS(on)}	Q1	--	74	103	mΩ
	V _{GS} = 4.5V, I _D = 2.3A			--	86	122	
	V _{GS} = -10V, I _D = -2A		Q2	--	135	180	
	V _{GS} = -4.5V, I _D = -1.7A			--	170	220	
Forward Transconductance ^(Note 3)	V _{DS} = 10V, I _D = 2.5A	g _{fs}	Q1	--	10	--	S
	V _{DS} = -10V, I _D = -2A		Q2	--	5	--	
Dynamic ^(Note 4)							
Total Gate Charge	Q1 V _{DS} = 30V, I _D = 2.5A Q2 V _{DS} = -30V, I _D = -2A	Q _{g(VGS=10V)}	Q1	--	9.4	--	nC
Total Gate Charge			Q2	--	9	--	
		Gate-Source Charge	Q _{g(VGS=4.5V)}	Q1	--	4.4	
Q2				--	4.6	--	
Gate-Drain Charge		Q _{gs}	Q1	--	1.8	--	
			Q2	--	1.2	--	
Input Capacitance	Q1 V _{GS} = 0V, V _{DS} = 30V	C _{iss}	Q1	--	527	--	pF
			Q2	--	436	--	
Output Capacitance	f = 1.0MHz Q2	C _{oss}	Q1	--	31	--	
			Q2	--	32	--	
Reverse Transfer Capacitance	V _{GS} = 0V, V _{DS} = -30V f = 1.0MHz	C _{rss}	Q1	--	4	--	
			Q2	--	11	--	
Gate Resistance	f = 1.0MHz	R _g	Q1	0.5	1.8	3.6	Ω
			Q2	5	17	34	
Switching ^(Note 4)							
Turn-On Delay Time	Q1 V _{GS} = 10V, V _{DS} = 30V, I _D = 2.5A, R _G = 2Ω Q2 V _{GS} = -10V, V _{DS} = -30V, I _D = -2A, R _G = 2Ω	t _{d(on)}	Q1	--	5	--	ns
Turn-On Rise Time			Q2	--	3.4	--	
		Turn-Off Delay Time	t _r	Q1	--	21	
Q2				--	21	--	
Turn-Off Fall Time		t _{d(off)}	Q1	--	10	--	
			Q2	--	21	--	
Turn-Off Fall Time		t _f	Q1	--	17	--	
			Q2	--	26	--	

ELECTRICAL SPECIFICATIONS ($T_A = 25^\circ\text{C}$ unless otherwise noted)							
PARAMETER	CONDITIONS	SYMBOL	TYPE	MIN	TYP	MAX	UNIT
Source-Drain Diode							
Forward Voltage (Note 3)	$V_{GS} = 0\text{V}, I_S = 2.5\text{A}$	V_{SD}	Q1	--	--	1	V
	$V_{GS} = 0\text{V}, I_S = -2\text{A}$		Q2	--	--	-1	
Reverse Recovery Time	Q1 $I_S = 2.5\text{A}, dI/dt = 100\text{A}/\mu\text{s}$	t_{rr}	Q1	--	14	--	ns
			Q2	--	11	--	
Reverse Recovery Charge	Q2 $I_S = -2\text{A}, dI/dt = 100\text{A}/\mu\text{s}$	Q_{rr}	Q1	--	10	--	nC
			Q2	--	6	--	

Notes:

- Current limited by package.
- Q1 : $L = 0.3\text{mH}$, $V_{GS} = 10\text{V}$, $V_{DD} = 30\text{V}$, $R_G = 25\Omega$, $I_{AS} = 6.8\text{A}$, Starting $T_J = 25^\circ\text{C}$
Q2 : $L = 0.3\text{mH}$, $V_{GS} = -10\text{V}$, $V_{DD} = -30\text{V}$, $R_G = 25\Omega$, $I_{AS} = -7\text{A}$, Starting $T_J = 25^\circ\text{C}$
- Pulse test: Pulse Width $\leq 300\mu\text{s}$, duty cycle $\leq 2\%$.
- Switching time is essentially independent of operating temperature.


ORDERING INFORMATION

ORDERING CODE	PACKAGE	PACKING
TSM8588CS RLG	SOP-8	2,500pcs / 13" Reel


CHARACTERISTICS CURVES (Q1 N-Channel)

($T_A = 25^\circ\text{C}$ unless otherwise noted)


Output Characteristics




Transfer Characteristics




On-Resistance vs. Drain Current




Gate-Source Voltage vs. Gate Charge



On-Resistance vs. Junction Temperature








On-Resistance vs. Gate-Source Voltage



CHARACTERISTICS CURVES


($T_A = 25^\circ\text{C}$ unless otherwise noted)




CHARACTERISTICS CURVES (Q2 P-Channel)

($T_A = 25^\circ\text{C}$ unless otherwise noted)


Output Characteristics




Transfer Characteristics




On-Resistance vs. Drain Current




Gate-Source Voltage vs. Gate Charge



On-Resistance vs. Junction Temperature




On-Resistance vs. Gate-Source Voltage




CHARACTERISTICS CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)


Capacitance vs. Drain-Source Voltage




BV_{DSS} vs. Junction Temperature




Maximum Safe Operating Area, Junction-to-Case



Source-Drain Diode Forward Current vs. Voltage




Normalized Thermal Transient Impedance, Junction-to-Case




PACKAGE OUTLINE DIMENSIONS (Unit: Millimeters)

SOP-8



SUGGESTED PAD LAYOUT (Unit: Millimeters)



MARKING DIAGRAM



Y = Year Code
WW = Week Code (01~52)
L = Lot Code (1~9,A~Z)
F = Factory Code

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.