



Part Number : [1200110238](#)
Product Description : Micro-Change (M12)
Receptacle, 5 Poles, M16x1.5 Mounting
Threads, Female (Straight), PCB Pins
Series Number : 120011
Status : Active
Product Category : Circular Industrial
Connectors
Engineering Number : 8R5J400013




Documents & Resources

Drawings
[1200110238_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead; Triphenyl-phosphate per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	120011
Description	Micro-Change (M12) Receptacle, 5 Poles, M16x1.5 Mounting Threads, Female (Straight), PCB Pins
IP Rating	IP67
NEMA Rating	NEMA 6
Product Name	Micro-Change (M12)
Type	PCB Mount
UPC	883906175979

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Physical

Coupling Type	Internal Thread
Gender	Female
Keyway	Single
Length	N/A
Material - Component	Nickel-plated Brass
Mounting Thread Size	PG9
Net Weight	22.679/g
Orientation	Straight
Panel Mount	Back
Poles	5
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	N/A
Wire Size (AWG)	N/A

This document was generated on Mar 22, 2025