

120W & 240W DIN Rail Mount Power Supplies

Features

- ◆ Low Cost
- ◆ 12V, 24V or 48V Outputs
- ◆ Auto-ranging input (no manual switching)
- ◆ Parallel Function Switch
- ◆ -40⁽²⁾ to +71°C Operation

Key Market Segments & Applications



Industrial



RoHS

Specifications



Model		DPP120-xx-1	DPP240-xx-1
AC Input Voltage range	VAC	93 - 132 / 186 - 264VAC, single phase. Auto select	
Input Frequency	Hz	47 - 63Hz	
DC Input Voltage range	VDC	210 - 370VDC*	
Inrush Current (115 / 230VAC)	A	24 / 48A	30 / 60A
Power Factor	-	Meets EN61000-3-2	
Input Current (115 / 230VAC)	A	2.8 / 1.4A	5.4 / 2.2A
Leakage Current	mA	3.5mA	
Output Voltage Accuracy	%	-0, +1% of Nominal	
Line Regulation	%	±0.5%	
Load Regulation	%	±1% (±5% when set in parallel mode)	
Ripple and Noise (20MHz BW)	mV	50mV	100mV
Overcurrent Protection (Typ)	-	110 - 145%	
Overvoltage Protection	V	See model selector	
Overtemperature Protection	-	-	
Hold Up Time (230VAC input)	ms	> 30ms	
Parallel operation	-	Set in parallel (droop) mode - maximum of 3 units	
LED Indicators	-	Green LED = On, Red LED = DC Output Low	
DC Good Relay (24V model only)	-	0.3A rated normally open relay contacts, closes when output is above 17.6 - 19.4V	
Operating Temperature	°C	-40 ⁽²⁾ to +71°C (Derate linearly 2.5%/°C from 61 to 71°C)	
Storage Temperature	°C	-40 to +85°C	
Operating Humidity	-	20 - 95% RH (non condensing)	
Cooling (1)	-	Convection	
Withstand Voltage	-	Input to Output 3kVAC for 1 min.	
Isolation Resistance	-	>100M at 25C & 70%RH, Output to Ground 500VDC	
Vibration (Operating)	-	IEC 60068-2-6 (Mounting by rail: Random wave, 10-500 Hz, 2G, ea. along X, Y, Z axes 10 min/cycle, 60 min)	
Shock (Operating)	-	IEC 60068-2-27 (Half sine wave, 4G, 22ms, 3 axes, 6 Faces, 3 times for each face)	
Safety Agency Approvals	-	UL508 Listed, IEC/UL/CSA/EN62368-1, 60950-1, CE Mark	
Conducted & Radiated EMI	-	EN55022 class B	EN55022 class A
Immunity	-	IEC 61000-4-2, -3, 4, -5, -6, -8, -11	
Weight (Typ)	g	920	1000
Size (LxWxH)	mm	116.6 x 63.5 x 125mm	116 x 83 x 125mm
Size (LxWxH) (1)	in	4.59 x 2.5 x 4.92"	4.57 x 3.27 x 4.92"
Case material	-	Metal	
Warranty	yrs	Three years	

(1) Recommend 1" clearance on all sides



(2) DPP120 -35°C

*Safety certified for AC input only

Outline Drawing (DPP120)



Outline Drawing (DPP240)



Model Selector

Model	Voltage	Adjust. Range	Output Curr.	Over-voltage	Eff.
DPP120-12-1	12V	11.4 - 14.5V	10A	15 - 17.4V	84%
DPP120-24-1	24V	22.5 - 28.5V	5A	30 - 34.8V	86%
DPP120-48-1	48V	45 - 55V	2.5A	60 - 69.6V	87%
DPP240-24-1	24V	22.5 - 28.5V	10A	30 - 34.8V	89%
DPP240-48-1	48V	47 - 56V	5A	60 - 69.6V	90%

Other DIN Rail Products

DPP	15W to 100W
DPP480	480W single and three phase
DSP	10W to 100W low profile
DLP	75W to 240W single phase

Terminal Assignments

#	Function
1	DC Good relay
2	DC Good relay
3	+V
4	+V
5	-V
6	-V
7	Chassis ground
8	L
9	N

Snap-on Mounting: snap onto DIN Rail TS35/7.5 or TS35/15. (no tools required)

Options

Suffix	Description
Blank	Non detachable connectors
B	Detachable input and output connectors

For Additional Information, please visit
<https://product.tdk.com/info/en/products/power/index.html>

