

- Find Distributor
- Contact Molex



**Status:** Active  
**Series:** [90151](#)  
**Category:** Molex Parts

**Low-Halogen Status:**Not Low-Halogen

## General

## Physical

UL E29179

## Solder Process Data

<b>Duration at Max. Process Temperature (seconds)</b>	002
<b>Lead-free Process Capability</b>	WAVE
<b>Max. Cycles at Max. Process Temperature</b>	001
<b>Process Temperature max. C</b>	210

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Products

- [Antennas](#)
- [Application Tooling](#)
- [Cable Assemblies](#)
- [Connected Lighting](#)
- [Connectors](#)
- [Copper Flex](#)
- [Electrical Products](#)
- [Industrial Automation](#)
- [Membrane Switches](#)
- [Optical Solutions](#)
- [Printed Electronic Solutions](#)

Quick Links

- [Company Information](#)
- [Contact Molex](#)
- [Cross-Reference](#)
- [Koch Industries](#)
- [Industries](#)
- [Literature](#)
- [Molex Racing](#)
- [Press Room / Press Releases](#)
- [Product Index](#)
- [Sitemap](#)

Resources

- [Supply Chain Transparency](#)
- [Business Continuity](#)
- [Compliance](#)
- [ecocare](#)
- [Feedback |](#)
- [Jobs](#)
- [Legal | Trade](#)
- [Mobile Site](#)
- [Supplier Po](#)
- [Privacy Poli](#)
- [Tradeshows](#)

Stay Connected



**Molex.com would like to place cookies on your computer to help us make this website better.**

To find out more about the cookies, see our [Privacy Policy](#). To accept cookies from this site, please click the 'I Accept' button.

I Accept

I Decline

Molex is a registered trademark of Molex, LLC in the United States of America and may be registered to their respective owners.