




REV.	ECR/ECN No.	DESCRIPTION	DRAWN/DATE	CHECKED/DATE	APPROVED/DATE
C	ECN2020073	Added H7.5 specification	Staven 2020-09-03	Staven 2020-09-03	Biao 2020-09-03
D	ECN2022112	UPDATE CPK SYMBOLS	Abner 2022-07-20	Staven 2022-07-20	Sam 2022-07-20





3D VIEW


NOTES:




- 1、 MATERIAL: C5210-EH T=0.10±0.01mm;
- 2、 BURR 0.03mm MAX.
- 3、 PLATING: Au 2u" SURFACE PLATING OVER CONTACT AREAS, Au 2u" SURFACE PLATING OVER SOLDER AREAS, Ni 40-120u" UNDER PLATING OVER ALL.
- 4、 ALL MATERIALS COMPLY WITH ROHS MANAGEMENT;
- 5、 WITH" ▼ "MUST BE CPK CONTROL.

TABLE:

PART NUMBER	A	B
Z016-4F7L1-11000-E000	4.80	1.50
Z02B-4F7L1-11000-E000	5.20	1.90
Z02D-4F7L1-11000-E000	7.50	4.20





UNLESS OTHERWISE SPECIFIED TOLERANCES				ANGLE OF PROJECTION 		 Amphenol Aorora Technology (Huizhou) Co.,Ltd			
X.	±0.30	X. *	± 5'			TITLE: H4.8/H5.2/7.5 SPRING T=0.1mm			
X.X	±0.25	X.X *	± 4'						
X.XX	±0.20	X.XX *	± 3'						
X.XXX	±0.15	X.XXX *	± 2'						
LINEAR DIMS		ANGLES DIMS							
DWG NO.: A-S0490				DOC Typ		Customer Drw			
DRAWN		DATE		Abner		SIZE A4			
DESIGN		DATE		Abner					
CHECKED		DATE		Staven					
APPROVED		DATE		Sam					
MATERIAL		SEE NOTES				PART NUMBER: Z0**-4F7L1-11000-E000			REV. D
FINISHED		SEE NOTES				SCALE 1:1			UNIT : mm
						SHEET 1			OF 1



REV.	ECR/ECN No.	DESCRIPTION	DRAWN/DATE	CHECKED/DATE	APPROVED/DATE
A	ECN2020001	NEW RELEASE	Staven 2020-03-17	Staven 2020-03-17	Biao 2020-03-17

NOTES:

- MATERIAL:
 - CARRY TAPE:HIPS,T=0.50mm,COLOR:TRANSPARENT.
 - REEL:HIPS,BLUE.
 - SHIM:PE,CLEAR.
- PRIMARY PACKING:900PCS/REEL.
- SECONDARY PACKING:14 REELS/CARTON
(12600=14*900/CARTON).
- PEELING RESISTANCE: 0.2N~1.2N(20~120gf);
PEELING ANGLE: 165°~180°;
PEELING SPEED: 300mm/minutes.



UNLESS OTHERWISE SPECIFIED TOLERANCES				ANGLE OF PROJECTION		Amphenol AORORA			
X.	±0.30	X. °	± 5'			Amphenol Aorora Technology (Huizhou) Co.,Ltd			
X.X	±0.25	X.X °	± 4'						
X.XX	±0.20	X.XX °	± 3'	DOC TYPE		TITLE:			
X.XXX	±0.15	X.XXX °	± 2'	PACKING Drw		H5.2 SPRING T=0.1mm PACKING			
LINEAR DIMS		ANGLES DIMS		DRAWN	DATE	Staven	2020-03-17	SIZE	
DWG NO.:		A-H0325		DESIGN	DATE	Staven	2020-03-17	PART NUMBER:	
MATERIAL		SEE NOTES		CHECKED	DATE	Biao	2020-03-17	Z02B-4F7L1-11000-E000	
FINISHED		SEE NOTES		APPROVED	DATE	Biao	2020-03-17	SCALE	
						1:1		UNIT : mm	
						SHEET		1 OF 1	