

# US-EMLP (35X15) - Plastic label



0830300

<https://www.phoenixcontact.com/us/products/0830300>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plastic label, Card, white, unmarked, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, THERMOMARK PRIME 2.0, mounting type: adhesive, Number of individual labels: 27, text field height: 15 mm, text field width: 35 mm

## Your advantages

- PVC material flammability rating V0 in accordance with UL 94
- The markers, which are supplied as uniform cards, can be labeled quickly, easily, and cost-effectively using the THERMOMARK CARD
- The perforated markers and labels are easy to separate and can be easily fitted
- The sheets provide space for including function texts
- The US-EMLP ... UniSheet labeling range includes self-adhesive device markers with good adhesive properties

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 0830300       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | BG09          |
| Product key                          | BG2419        |
| GTIN                                 | 4046356715157 |
| Weight per piece (including packing) | 18.69 g       |
| Weight per piece (excluding packing) | 17.9 g        |
| Customs tariff number                | 39199080      |
| Country of origin                    | DE            |

# US-EMLP (35X15) - Plastic label



0830300

<https://www.phoenixcontact.com/us/products/0830300>

## Technical data

### Product properties

|                                     |                                                          |
|-------------------------------------|----------------------------------------------------------|
| Product type                        | Device marking                                           |
| Marking                             |                                                          |
| Number of individual labels         | 27                                                       |
| Number of individual labels per row | 3                                                        |
| Identification technology           | Thermal transfer for sheets and cards, UV LED technology |

### Mounting

|               |          |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

### Material specifications

|                   |                  |
|-------------------|------------------|
| RoHS compliant    | yes              |
| Foil strength     | 500 µm           |
| Adhesive strength | 50 µm            |
| Adhesive          | Acrylic          |
| Color             | white (RAL 9010) |
| Material          | PVC              |
| Components        | Silicone-free    |

### Environmental and real-life conditions

#### Test for substances that would hinder coating with paint or varnish

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

#### UV resistance

|               |                                |
|---------------|--------------------------------|
| Specification | ISO 4892-2:2013-03 (following) |
| Result        | Test passed                    |
| Test duration | 96 h                           |

#### Wipe resistance of inscriptions

|                                                 |                                                |
|-------------------------------------------------|------------------------------------------------|
| Specification                                   | DIN EN 61010-1 (VDE 0411-1):2011-07            |
|                                                 | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropyl<br>[CAS No. 67-63-0]                  | Test passed                                    |
| n-Hexane<br>[CAS No. 110-54-3]                  | Test passed                                    |
| Water + Petroleum ether<br>[CAS No. 64742-82-1] | Test passed                                    |

#### Testing in a condensation changing climate in the presence of sulfur dioxide

|               |                   |
|---------------|-------------------|
| Specification | DIN 50018:2013-05 |
| Result        | Test passed       |
| Climate level | AHT 1.0 S         |
| Cycles        | 2                 |

# US-EMLP (35X15) - Plastic label



0830300

<https://www.phoenixcontact.com/us/products/0830300>

## Salt spray test

|               |                           |
|---------------|---------------------------|
| Specification | DIN EN 60068-2-11:2000-02 |
| Result        | Test passed               |

## Ambient conditions

|                                                     |                                                                                                         |
|-----------------------------------------------------|---------------------------------------------------------------------------------------------------------|
| Ambient temperature (operation)                     | -30 °C ... 80 °C                                                                                        |
| Recommended storage conditions                      | 23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended. |
| Recommended ambient temperature (storage/transport) | 23 °C                                                                                                   |
| Recommended humidity (storage/transport)            | 50 %                                                                                                    |
| Shelf life                                          | 12 months                                                                                               |

## Dimensions

|        |          |
|--------|----------|
| Width  | 34.65 mm |
| Height | 14.9 mm  |
| Depth  | 0.55 mm  |

## Text field

|                   |       |
|-------------------|-------|
| Text field width  | 35 mm |
| Text field height | 15 mm |

## Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

# US-EMLP (35X15) - Plastic label

0830300

<https://www.phoenixcontact.com/us/products/0830300>



## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0830300>



**CSA**

Approval ID: 70191766

# US-EMLP (35X15) - Plastic label

0830300

<https://www.phoenixcontact.com/us/products/0830300>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281103 |
| ECLASS-15.0 | 27281103 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001288 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

# US-EMLP (35X15) - Plastic label



0830300  
<https://www.phoenixcontact.com/us/products/0830300>

## Environmental product compliance

|                                         |                            |
|-----------------------------------------|----------------------------|
| EU RoHS                                 |                            |
| Fulfills EU RoHS substance requirements | Yes, No exemptions         |
| EU REACH SVHC                           |                            |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt% |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)