

NEW

## Vibro Motor click

**PID:** MIKROE-2826

**Weight:** 24 g

Hover to zoom


**Vibro Motor click** features a compact size Eccentric Rotating Mass (ERM) motor, labeled as [C1026B002F](#). This type of motor is often used for haptic feedback on many small handheld devices, such as the cellphones, pagers, RFID scanners and similar devices. This motor contains a small eccentric weight on its rotor, so while rotating it also produces vibration effect. This kind of motors is sometimes referred to as coin motors, due to its shape.

Besides the vibration motor, the click is also equipped with the DMG3420U, a small MOSFET, which is used to drive the motor. The Vibro Motor click is an ideal solution for adding a simple, one pin driven haptic feedback on any design.

Quantity

1


 Add to Cart


Looking for customized version of this product?



If you have other questions about this product contact us here.

 LEAVE A MESSAGE

## Table of contents

1. [How does it work?](#)
2. [Specifications](#)
3. [Pinout diagram](#)
4. [Vibro Motor click specifications](#)
5. [Onboard settings and indicators](#)
6. [Software support](#)
7. [mikroSDK](#)
8. [Downloads](#)

An error occurred.

[Try watching this video on www.youtube.com, or enable JavaScript if it is disabled in your browser.](#)

**Vibro Motor click** features a compact size Eccentric Rotating Mass (ERM) motor, labeled as [C1026B002F](#). This type of motor is often used for haptic feedback on many small handheld devices, such as the cellphones, pagers, RFID scanners and similar devices. This motor contains a small eccentric weight on its rotor, so while rotating it also produces vibration effect. This

kind of motors is sometimes referred to as coin motors, due to its shape.

Besides the vibration motor, the click is also equipped with the DMG3420U, a small MOSFET, which is used to drive the motor. The Vibro Motor click is an ideal solution for adding a simple, one pin driven haptic feedback on any design.

## How does it work?

The click uses the DMG3420U MOSFET to drive the ERM motor, since the MCU itself cannot provide enough power for the motor driving. The circuit also contains a protection diode, which is used to protect the transistor from the reverse voltage, since the motor represents an inductive load and turning off its current can produce a kickback voltage that can damage the transistor.



The gate of the MOSFET is driven by the PWM signal, routed through the PWM pin of the mikroBUS™. The PWM signal toggles the gate of the MOSFET with the pulses of a certain width. As a result, the current through the motor is varied depending on the pulse width of the PWM signal, which directly affects the speed of the motor, effectively controlling the vibration force that way. The small, eccentric weight attached to the rotor of the coin motor, generates the centrifugal force while it rotates, which in turn results with the wobbling effect of the motor itself. The faster the rotation is, the bigger the force gets. Controlling the motor speed allows for the vibration intensity to be controlled.

MikroElektronika library contains functions that are used to easily drive the motor by changing the PWM pulse width, saving time for the application firmware development.

## Specifications

|              |  |
|--------------|--|
| Type         | DC   |
| Applications | An ideal solution for adding a simple, one pin driven haptic feedback on any design. |
| Key Features | Low power consumption, compact size  |
| Interface    | PWM  |

|                  |                    |  |  |  |  |
|------------------|--------------------|--|--|--|--|
| Input Voltage    | 3.3V               |  |  |  |  |
| Click board size | M (42.9 x 25.4 mm) |  |  |  |  |

## Pinout diagram

This table shows how the pinout on **Vibro Motor click** corresponds to the pinout on the mikroBUS™ socket (the latter shown in the two middle columns).

| Notes        | Pin        | mikro™<br>BUS |      |     |    |            | Pin    | Notes               |
|--------------|------------|---------------|------|-----|----|------------|--------|---------------------|
|              | NC         | 1             | AN   | PWM | 16 | <b>PWM</b> |        | Motor speed control |
|              | NC         | 2             | RST  | INT | 15 | NC         |        |                     |
|              | NC         | 3             | CS   | RX  | 14 | NC         |        |                     |
|              | NC         | 4             | SCK  | TX  | 13 | NC         |        |                     |
|              | NC         | 5             | MISO | SCL | 12 | NC         |        |                     |
|              | NC         | 6             | MOSI | SDA | 11 | NC         |        |                     |
| Power supply | <b>3V3</b> | 7             | 3.3V | 5V  | 10 | NC         |        |                     |
| Ground       | <b>GND</b> | 8             | GND  | GND | 9  | <b>GND</b> | Ground |                     |

## Vibro Motor click specifications

| Description                 | Min  | Typ | Max | Unit |
|-----------------------------|------|-----|-----|------|
| Rated ERM motor speed       | 9000 |     |     | RPM  |
| Bracket deflection strength |      | 9.8 |     | N    |
| Mechanical noise            |      |     | 50  | dB   |
| Operating Temperature       | -20  |     | +60 | °C   |

## Onboard settings and indicators

| Label | Name        | Default | Description         |
|-------|-------------|---------|---------------------|
| VM    | Vibro motor | -       | Vibration motor     |
| PWR   | Power LED   | -       | Power LED indicator |

## Software support

We provide an example for Vibro Motor click on our [LibStock](#) page, as well as a demo application (example), developed using MikroElektronika [compilers](#). The demo can run on all the main MikroElektronika [development boards](#).

## Examples description

This demo application demonstrates how to control Vibro Motor click by using the MCU's PWM module. The demo application is composed of two sections:

- `systemInit` - Initializes the PWM module
- `applicationTask` - Sequential call of each pattern with 1 second delay in between

### Additional functions:

`void vibromotor_pattern1(uint8_t loops)` - Long vibration pattern - 1 second vibration + 1 second delay

`void vibromotor_pattern2(uint8_t loops)` - Short vibration pattern - 200 ms vibration + 500 ms delay

The full application code and ready to use projects can be found on our [LibStock](#) page.

Other mikroE Libraries used in the example:

- PWM

### Additional notes and information

Depending on the development board you are using, you may need [USB UART click](#), [USB UART 2 click](#) or [RS232 click](#) to connect to your PC, for development systems with no UART to USB interface available on the board. The terminal available in all MikroElektronika [compilers](#), or any other terminal application of your choice, can be used to read the message.

## mikroSDK

This click board is supported with mikroSDK, the MikroElektronika Software Development Kit. To download mikroSDK visit [LibStock](#). For more information about SDK, visit the [official page](#).

## Downloads



[mikroBUS™ standard specifications](#)



[LibStock Vibro Motor click library](#)



[C1026B002F datasheet](#)



[Vibro Motor click schematic](#)

## PRODUCTS IN THE SAME CATEGORY

Subscribe to our newsletter:

 

Follow us on:



**PRODUCT LINES**

[click Boards™](#) | [Compilers](#) | [Development Boards](#) | [Smart Displays](#) | [Programmers](#) | [Development Kits](#) |  
[Customization](#)

**TOOLCHAINS**

[PIC](#) | [dsPIC](#) | [PIC32](#) | [ARM](#) | [AVR](#) | [FT90x](#) | [8051](#)

**COMPANY**

[About us](#) | [Contact](#) | [Support](#) | [Distributors](#) | [Careers](#) | [Internship](#) | [Make a click™ program](#)

**RESOURCES**

[mikroBUS™](#) | [mikroSDK](#) | [Hexiwear™](#) | [Libstock™](#) | [Blog](#) | [eBooks](#) | [Forum](#) | [Outlet](#) | [Legacy Products](#)

Copyright© 2017 MikroElektronika d.o.o. | [Terms and Conditions](#) | [Privacy Policy](#)