

North America: Danboro, PA • E-mail: info@pemnet.com • Tel: +1-215-766-8853


Europe: Galway, Ireland • E-mail: europe@pemnet.com • Tel: +353-91-751714

Asia/Pacific: Singapore • E-mail: singapore@pemnet.com • Tel: +65-6-745-0660

Shanghai, China • E-mail: china@pemnet.com • Tel: +86-21-5868-3688

Part # KFSE-143-16, Broaching Standoffs - Types KFE, KFSE - Unified

Type KFE and KFSE - Broaching standoffs, threaded or unthreaded for stacking or spacing.



Specifications

Thru Hole + .004 -.003 .143 in

Thru-Hole Code 143

Length Code 16

A (Shank) Max. .060 in

Min. Sheet Thickness .060 in

Hole Size in Sheet + .003 - .000 .213 in

C ± .003 .231 in



E ± .005 .281 in

L - Length ± .005 .500 in

Min. Dist. Hole C/L to Edge .22 in

For Use in Sheet Hardness¹	HRB 70 / HB 125 or Less PC Board
Fastener Material	300 Series Stainless Steel
Standard Finish	Passivated and/or tested per ASTM A380
CAD Supplier	PennEngineering® (PEM®)

¹ HRB - Hardness Rockwell "B" Scale. HB - Hardness Brinell.